







The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited.
Offenders will be held liable for the payment of damages. Weidmüller exclusively reserves the right to file for patents, utility models or designs.

© Weidmüller Interface GmbH & Co. KG

The English version is binding



Drehmoment
Torque 2.5 Nm $\pm$ 0.5



Darstellung mit Zubehoer
Shown with accessory 9536040000 MF FPC

General Tolerances: ISO 2768:1989-m

Tolerances ISO 8015

Changes: EC00011185

0

Mat. No. (SAP) 2975550000

Drawings Assembly

Drawn Dreier, Bianca

Responsible Wohlgemuth, Klaus

Approved Püschner, Klaus

13.06.2024



Weidmüller



80315

Drawing no.

Scale: 1:4

Sheet 3 / 4

1

Index

PVN DC 2I 10 3MPP SPD2R WM4 11

COMBINERBOX RESIDENTIAL/COMMERCIAL

COMBINERBOX RESIDENTIAL/COMMERCIAL

A3