

**EDS file change-log of new features, bug fixes and new supported modules of the  
u-remote field bus coupler: 1334890000 UR20-FBC-CAN  
EDS file: WI133489V1\_31.eds**

---

**Version 01.32****Release date: February, 2025**

New version (identical to 01.31)

---

**Version 01.31****Release date: October, 2024****New supported modules:**

- 2920830000 - UR20-3EM-400V-AC-CT1A
- 2920840000 - UR20-3EM-400V-AC-CT5A
- 2920850000 - UR20-3EM-400V-AC-RC
- 2920860000 - UR20-3EM-400V-AC-333MV
- 2489840000 - UR20-1COM-CAN

---

**Version 01.29****Release date: June 2024****New supported modules:**

- 3036960000 - UR20-2PWM-PN-0.5A-V2
- 3036950000 - UR20-2PWM-PN-2A-V2

---

**Version 01.27****Release date: November 2023****New supported modules:**

- 2489840000 - UR20-1COM-CANOPEN

---

**Version 01.26****Release date: August 2022****New supported modules:**

- 2697910000 UR20-2PWM-I-2.5A-2DI-P

---

**Version 01.24****Release date: February 2022****New supported modules:**

- 2826800000 UR20-1COM-232-485-422-V2

---

**Version 01.22****Release date: February 2021****New feature:**

- Support of new version of UR20-2AI-SG-24-DIAG with MX file 001051.110 which is calibrated for an extended range of sensor sensitivity up to 960mV/V. **CAUTION:** Modules with MX file versions below 001501.110 are calibrated for a maximum sensor sensitivity range of 30mV/V and will return no valid measurement values if used outside this range!

**New supported modules:**

- 2705620000 UR20-2AI-UI-16
- 2566090000 UR20-2AI-UI-16-DIAG
- 2705630000 UR20-2AO-UI-16
- 2566100000 UR20-2AO-UI-16-DIAG

---

**Version 01.19****Release date: March 2020****New supported modules:**

- 2566960000 UR20-4AI-UI-ISO-16-DIAG
- 2566970000 UR20-2AO-UI-ISO-16-DIAG

---

**Version 01.18****Release date: July 2019****New feature:**

- Support of slave-to-slave communication

---

**Version 01.17****Release date: March 2019**

**New supported modules:**

- 1315740000 - UR20-4COM-IO-LINK

**Version 01.16****Release date: July 2018****New supported modules:**

- 2489830000 - UR20-1SM-50W-6DI2DO-P
- 2456530000 - UR20-8DIO-P-3W-DIAG
- 2544660000 - UR20-4AI-UI-DIF-32-DIAG
- 2555940000 - UR20-8AI-RTD-DIAG-2W

**Version 01.15****Release date: December 2017****New supported modules:**

- 2457250000 - UR20-4DO-ISO-4A
- 2457240000 - UR20-8DI-ISO-2W

**Version 01.14****Release date: May 15, 2017****New supported modules:**

- 2456540000 - UR20-4AI-RTD-HP-DIAG
- 2453880000 - UR20-4AO-UI-16-M
- 2453870000 - UR20-4AO-UI-16-M-DIAG

**Version 01.13****Release date: October 06, 2016****New supported module:**

- 1990070000 UR20-2AI-SG-DIAG

**Version 01.12****Release date: June 06, 2016****New supported modules:**

- 2001670000 UR20-4AI-R-HS-16-DIAG
- 2007420000 UR20-3EM-230V-AC
- 1993880000 UR20-4AI-UI-DIF-16-DIAG
- 1315400000 UR20-16DI-N-PLC-INT
- 1315450000 UR20-16DO-N-PLC-INT

**Version 01.10****Release date: February 02, 2016****New supported modules:**

- 1315440000 UR20-16DO-N
- 1315750000 UR20-1COM-232-485-422
- 2007430000 UR20-1COM-SAI-PRO

**Version 01.09****Release date: July 23, 2015**

First released version

**New features:**

- New web server ([Manual u-remote web server online](#))
- Default password for the web server

**The following modules are not compatible with the coupler:**

- 1460140000 UR20-2DI-P-TS
- 1460150000 UR20-4DI-P-TS
- 1335060000 UR20-4DI-4DO-PN-FSPS
- 1335070000 UR20-8DI-PN-FSPS
- 1529780000 UR20-4DI-4DO-PN-FSOE
- 1529800000 UR20-8DI-PN-FSOE