



CERTIFICATE

No. B 033299 0512 Rev. 02

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product: Power supply
(Din-Rail Diode Module)

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6821020022504

Valid until: 2031-06-23

Date, 2026-06-24

(Yager Bi)



CERTIFICATE

No. B 033299 0512 Rev. 02

Model(s): PRO DM 10, PRO DM 20

Brand Name: Weidmüller



Parameters:

Ratings:

Input/Operational voltage: 5-48VDC/0-60VDC

Input/Output current: 2X10A/1X20A (for model PRO DM 10)

Input/Output current: 2X20A/1X40A (for model PRO DM 20)

Degree of Protection: IPX0

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- The maximum operating temperature is 70°C.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- Built-in type equipment, suitable enclosure should be provided by end system.
- The input voltage tolerance is 0-60VDC.
- When installed the equipment, keep min. 10cm distance for bottom openings for ventilation.

Tested according to: EN IEC 62368-1:2024/A11:2024