



CERTIFICATE

No. B 033299 0473 Rev. 02

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product: Converter
(DC-DC Converter)

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6821020006105

Valid until: 2031-06-22

Date, 2026-06-23

(Yager Bi)



CERTIFICATE

No. B 033299 0473 Rev. 02

Model(s): PRO DCDC 240W 24V 10A

Brand Name: Weidmüller



Parameters:

Rated Input: 24VDC, 14A
Rated Output: 24VDC, 10A
Degree of Protection: IPX0

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Built-in type equipment, suitable enclosure should be provided by end system.
- The maximum operating temperature is 70°C. Refer to the installation and operating instruction from manufacturer for the details of loading condition and operating temperature.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- The input voltage tolerance is 18-32VDC.
- Functional insulation is provided between the input circuit and output circuit, and between input circuit and metal enclosure.
- This built-in equipment should be connected to a source which is insulated from the mains supply by double or reinforced insulation.

Tested according to: EN IEC 62368-1:2024/A11:2024