


Weidmüller 


THE REPRODUCTION, DISTRIBUTION AND USE OF THIS DOCUMENT AS WELL AS THE DISSEMINATION OF THE CONTENTS TO OTHERS WITHOUT AUTHORIZATION IS PROHIBITED.

-UC2
/99.b.1
/99.c.5


99.c.9 / SPD MPP 1/2



033
OG



034
OG



SPD MPP 7/8 / 99.b.3

025
BK


026
BK

027
BK

SPD5/6:PE / 99.c.6

SPD3/4:PE / 99.c.6


SPD1/2:PE / 99.c.6



0	Initial Version	15.08.2025	O. Behring	Edited by		Project description PVC DC 2I 20 12MPP SPD1R CG 11	Page description Customer schematic		Designation: 3165170000		Index 0	Installation site =
			O. Behring									Mounting location +
			O. Behring									Page 99.a
Index	Brief description	Date	Name	15.08.2025	O. Behring							Total no. of pages 13

THE REPRODUCTION, DISTRIBUTION AND USE OF THIS DOCUMENT AS WELL AS THE DISSEMINATION OF THE CONTENTS TO OTHERS WITHOUT AUTHORIZATION IS PROHIBITED.

-UC2
/99.a.1
/99.c.5



0	Initial Version	15.08.2025	O. Behring	Edited by		Project description PVC DC 2I 2O 12MPP SPD1R CG 11	Page description Customer schematic		Designation: 3165170000		Index 0	Installation site	=
			O. Behring									Mounting location	+
			O. Behring									Page	99.b
Index	Brief description	Date	Name	15.08.2025	O. Behring							Total no. of pages	13

0	Initial Version	15.08.2025	O. Behring	Edited by		Project description PVC DC 2I 2O 12MPP SPD1R CG 11	Page description Customer schematic		Designation: 3165170000		Index 0	Installation site =
			O. Behring	Date	Name							Mounting location +
			O. Behring	15.08.2025	O. Behring							Page 99.c
Index	Brief description	Date	Name									Total no. of pages 13