


WEIDMÜLLER SOWIE VERTEILUNG DIESE DOKUMENTS. VERWERTUNG UND MITTELUNG SEINER INHALTS SIND VERBOTEN, SOWEIT NICHT AUSDRÜCKLICH GESTATET.
ZUMERHANDLUNGEN VERPFLICHTEN ZU SCHADENSATZ ALLE RECHTE FÜR DEN FALL DER PATENT-, GEBRAUCHSMUSTER- ODER GESCHMACKSMUSTERRECHTUNG VORBEHALTEN.
THE REPRODUCTION OR DISTRIBUTION OF THIS DOCUMENT WITHOUT THE WRITTEN PERMISSION OF WEIDMÜLLER IS PROHIBITED. WEIDMÜLLER SOWIE VERTEILUNG DIESE DOKUMENTS. VERWERTUNG UND MITTELUNG SEINER INHALTS SIND VERBOTEN, SOWEIT NICHT AUSDRÜCKLICH GESTATET.
ZUMERHANDLUNGEN VERPFLICHTEN ZU SCHADENSATZ ALLE RECHTE FÜR DEN FALL DER PATENT-, GEBRAUCHSMUSTER- ODER GESCHMACKSMUSTERRECHTUNG VORBEHALTEN.
THE REPRODUCTION OR DISTRIBUTION OF THIS DOCUMENT WITHOUT THE WRITTEN PERMISSION OF WEIDMÜLLER IS PROHIBITED.



Additional product documents				1.				Tolerances: ISO 2768-mK			B		
				2.									
					Date	Name		Weidmüller					
				Drawn	17/12/2020	wes0362							
				Checked									
				Criterion for print				Description: PV 40201S2V4C2A1ES					
				1 : 1		A3							
				Customer:									
				Customer-No:									
0			17/12/2020	wes0362	Customer-No:				Drawing-No / Material-No: 8000069111		drw Index 0	Sheet 1 / 1	A
Index	Brief Description			Date	Name	Customer Description:							