

Overview about supported modules and required software and device description file versions for fieldbus coupler: 1334920000 UR20-FBC-EIP

Firmware updating Information:

An update of the firmware can be done via the embedded web server.

A description of the firmware update can be found in the u-remote web server manual on the Weidmüller website: www.weidmueller.com

Active modules

Module	HW V. 1.xx.xx Coupler SW / EDS	HW V. 2.xx.xx Coupler SW / EDS / L5K
1315390000 UR20-16DI-N	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315400000 UR20-16DI-N-PLC-INT	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315580000 UR20-1CNT-500	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1508090000 UR20-1SSI	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1550070000 UR20-4DI-2W-230V-AC	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315350000 UR20-4DI-N	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315410000 UR20-4DO-N	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315420000 UR20-4DO-N-2A	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315370000 UR20-8DI-N-3W	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315570000 UR20-1CNT-100-1DO	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315590000 UR20-2CNT-100	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315430000 UR20-8DO-N	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315200000 UR20-16DI-P	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315210000 UR20-16DI-P-PLC-INT	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315250000 UR20-16DO-P	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315270000 UR20-16DO-P-PLC-INT	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1460140000 UR20-2DI-P-TS	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315600000 UR20-2PWM-PN-0.5A	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315610000 UR20-2PWM-PN-2A	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315700000 UR20-4AI-RTD-DIAG	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315710000 UR20-4AI-TC-DIAG	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1394390000 UR20-4AI-UI-12	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315620000 UR20-4AI-UI-16	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315680000 UR20-4AO-UI-16	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315170000 UR20-4DI-P	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1460150000 UR20-4DI-P-TS	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315220000 UR20-4DO-P	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315230000 UR20-4DO-P-2A	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1394420000 UR20-4DO-PN-2A	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315550000 UR20-4RO-CO-255	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315670000 UR20-8AI-I-PLC-INT	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315180000 UR20-8DI-P-2W	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1394400000 UR20-8DI-P-3W	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315240000 UR20-8DO-P	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25

1335030000	UR20-PF-O-1DI-SIL	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1335040000	UR20-PF-O-2DI-DELAY-SIL	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1335050000	UR20-PF-O-2DI-SIL	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315690000	UR20-4AI-UI-16-DIAG	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1506920000	UR20-4AI-UI-16-HD	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315730000	UR20-4AO-UI-16-DIAG	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1506930000	UR20-4AO-UI-16-DIAG-HD	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315540000	UR20-4RO-SSR-255	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315190000	UR20-8DI-P-3W-HD	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1506910000	UR20-4AI-UI-16-DIAG-HD	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1510690000	UR20-4AO-UI-16-HD	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1508080000	UR20-2FCNT-100	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
2009360000	UR20-4DI-P-3W	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315720000	UR20-8AI-I-16-DIAG-HD	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315650000	UR20-8AI-I-16-HD	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1509830000	UR20-8DO-P-2W-HD	>= 01.00.15 / >= 1.0	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315440000	UR20-16DO-N	>= 01.00.19 / >= 1.1	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315750000	UR20-1COM-232-485-422	>= 01.00.19 / >= 1.1	>= 01.02.00 / >= 1.4 / >= 2020_06_25
2007430000	UR20-1COM-SAI-PRO	>= 01.00.19 / >= 1.1	>= 01.02.00 / >= 1.4 / >= 2020_06_25
	SAI subbus modules IP67	>= 01.00.19 / >= 1.1	>= 01.02.00 / >= 1.4 / >= 2020_06_25
2001670000	UR20-4AI-R-HS-16-DIAG	>= 01.00.22 / >= 1.1	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1993880000	UR20-4AI-UI-DIF-16-DIAG	>= 01.00.22 / >= 1.1	>= 01.02.00 / >= 1.4 / >= 2020_06_25
2007420000	UR20-3EM-230V-AC	>= 01.00.22 / >= 1.1	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1315450000	UR20-16DO-N-PLC-INT	>= 01.00.22 / >= 1.1	>= 01.02.00 / >= 1.4 / >= 2020_06_25
1990070000	UR20-2AI-SG-24-DIAG	>= 01.01.00 / >= 1.1	>= 01.02.00 / >= 1.4 / >= 2020_06_25
2453870000	UR20-4AO-UI-16-M-DIAG	>= 01.02.01 / >= 1.4	>= 01.02.00 / >= 1.4 / >= 2020_06_25
2453880000	UR20-4AO-UI-16-M	>= 01.02.01 / >= 1.4	>= 01.02.00 / >= 1.4 / >= 2020_06_25
2456540000	UR20-4AI-RTD-HP-DIAG	>= 01.02.01 / >= 1.4	>= 01.02.00 / >= 1.4 / >= 2020_06_25
2457250000	UR20-4DO-ISO-4A	>= 01.03.00 / >= 1.5	>= 02.03.00 / >= 1.5 / >= 2020_06_25
2457240000	UR20-8DI-ISO-2W	>= 01.03.00 / >= 1.5	>= 02.03.00 / >= 1.5 / >= 2020_06_25
2489830000	UR20-1SM-50W-6DI2DO-P	>= 01.05.00 / >= 1.5	>= 02.05.00 / >= 1.5 / >= 2020_06_25
2544660000	UR20-4AI-UI-DIF-32-DIAG	>= 01.05.00 / >= 1.5	>= 02.05.00 / >= 1.5 / >= 2020_06_25
2555940000	UR20-8AI-RTD-DIAG-2W	>= 01.05.00 / >= 1.5	>= 02.05.00 / >= 1.5 / >= 2020_06_25
2456530000	UR20-8DIO-P-3W-DIAG	>= 01.05.00 / >= 1.5	>= 02.05.00 / >= 1.5 / >= 2020_06_25
1315740000	UR20-4COM-IO-LINK	>= 01.07.00 / >= 1.5	>= 02.07.00 / >= 1.5 / >= 2020_06_25
2566960000	UR20-4AI-UI-ISO-16-DIAG	Not supported	>= 02.09.00 / >= 1.6 / >= 2020_06_25
2566970000	UR20-2AO-UI-ISO-16-DIAG	Not supported	>= 02.09.00 / >= 1.6 / >= 2020_06_25
2705620000	UR20-2AI-UI-16	Not supported	>= 02.11.00 / >= 1.6 / >= 2020_12_02
2566090000	UR20-2AI-UI-16-DIAG	Not supported	>= 02.11.00 / >= 1.6 / >= 2020_12_02
2705630000	UR20-2AO-UI-16	Not supported	>= 02.11.00 / >= 1.6 / >= 2020_12_02
2566100000	UR20-2AO-UI-16-DIAG	Not supported	>= 02.11.00 / >= 1.6 / >= 2020_12_02
2617520000	UR20-4AI-I-HART-16-DIAG	Not supported	>= 02.11.00 / >= 1.6 / >= 2020_12_02
2826800000	UR20-1COM-232-485-422-V2	Not supported	>= 02.12.00 / >= 1.6 / >= 2021_12_15
2697910000	UR20-2PWM-I-2.5A-2DI-P	Not supported	>= 02.13.00 / >= 1.6 / >= 2022_06_02
2489840000	UR20-1COM-CANOPEN	Not supported	>= 02.14.00 / >= 1.6 / >= 2023_07_03
2828350000	UR20-4AI-I-HART-ISO-16	Not supported	>= 02.14.00 / >= 1.6 / >= 2023_07_03
3036960000	UR20-2PWM-PN-0.5A-V2	Not supported	>= 02.14.00 / >= 1.6 / >= 2024_06_13
3036950000	UR20-2PWM-PN-2A-V2	Not supported	>= 02.14.00 / >= 1.6 / >= 2024_06_13
2920830000	UR20-3EM-400V-AC-CT1A	Not supported	>= 02.15.00 / >= 1.6 / >= 2024_07_23
2920840000	UR20-3EM-400V-AC-CT5A	Not supported	>= 02.15.00 / >= 1.6 / >= 2024_07_23

2920850000	UR20-3EM-400V-AC-RC	Not supported	>= 02.15.00 / >= 1.6 / >= 2024_07_23
2920860000	UR20-3EM-400V-AC-333MV	Not supported	>= 02.15.00 / >= 1.6 / >= 2024_07_23
3040800000	UR20-1COM-CAN	Not supported	>= 02.15.00 / >= 1.6 / >= 2024_07_23
1335060000	UR20-4DI-4DO-PN-FSPS	Not supported	Not supported
1335070000	UR20-8DI-PN-FSPS	Not supported	Not supported
1529780000	UR20-4DI-4DO-PN-FSOE	Not supported	Not supported
1529800000	UR20-8DI-PN-FSOE	Not supported	Not supported
2464570000	UR20-4DI-4DO-PN-FSPS-V2	Not supported	Not supported
2464590000	UR20-8DI-PN-FSPS-V2	Not supported	Not supported
2464600000	UR20-8DI-PN-FSOE-V2	Not supported	Not supported
2464580000	UR20-4DI-4DO-PN-FSOE-V2	Not supported	Not supported
2464060000	UR20-16DO-N-PLC-INT-30	Not supported	Not supported
2464050000	UR20-16DI-N-PLC-INT-30	Not supported	Not supported

Passive modules

1334790000	UR20-16AUX-FE	Not applicable
1334800000	UR20-16AUX-GND-I	Not applicable
1334810000	UR20-16AUX-GND-O	Not applicable
1334770000	UR20-16AUX-I	Not applicable
1334780000	UR20-16AUX-O	Not applicable
1315770000	UR20-ES	Not applicable
1334710000	UR20-PF-I	Not applicable