



WORKPLACE
SOLUTIONS

Workplace Solutions

THM MultiMark Plus R & R-Fix Thermal Transfer Printers

Quick, clean, reliable – professional labeling for wires and cables

The THM MultiMark Plus R printer, along with the new MultiMark R-Fix applicator, streamlines cable marking with wrap-around labels – making the process significantly faster and easier.

Labels are automatically applied and precisely wrapped around the cable – in just three seconds per marking. This provides time-savings up to 60%, compared to manual labeling.

High-quality application ensures minimal waste and maximizes the durability of each label through the lamination process.

Features & Benefits

- Fully automatic printing and wrapping process
- Efficient marking maximizes planning reliability
- High-quality, fast and accurate marking
- Increase efficiency up to 60% compared to manual application
- Durable marking due to lamination process
- Applicator's high production quality reduces waste and increases the marking's lifetime



More information on our website:
www.weidmuller.com/multimark

Maximum Performance with Minimal Effort

Thoughtful technology for your daily marking routine

Our labels are available in various sizes and reliably cover conductor outer diameters from 2 mm to 14 mm. This provides maximum flexibility for a wide range of applications. A high-quality lamination further protects against environmental influences and ensures permanently legible markings — even under demanding conditions.

Efficient marking with maximum planning reliability

Control via proven M-Print® PRO software

Fully automated printing and wrapping process

Reduces errors in the marking process



Efficiency increase of up to 60% compared to manual application

Lamination process provides permanent marking thanks to high resistance to external influences

| Type | Order no. |
|---------------------------|------------|
| THM MultiMark Plus R | 2931840000 |
| MultiMark R-Fix | 2931850000 |
| THM WO-R VIN 12.7/19.1 WS | 2932070000 |
| THM WO-R VIN 12.7/38.1 WS | 2932100000 |
| THM WO-R VIN 25.4/19.1 WS | 2932080000 |
| THM WO-R VIN 25.4/25.4 WS | 2932090000 |
| THM WO-R VIN 25.4/31.8 WS | 2932130000 |
| THM WO-R VIN 25.4/38.1 WS | 2932110000 |
| THM WO-R VIN 25.4/57.2 WS | 3062890000 |
| THM WO-R VIN 25.4/63.5 WS | 2932120000 |

Discover the future of workplace solutions —
experience state-of-the-art marking with our thermal transfer printers

Contact us today at weidmuller.com/sales to learn more!



eshop.weidmueller.com