





03

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited.  
Offenders will be held liable for the payment of damages. Weidmüller exclusively reserves the right to file for patents, utility models or designs.

© Weidmüller Interface GmbH & Co. KG




WGK4/Z...

WGK4...

KUNDENZEICHNUNG  
CUSTOMER DRAWING

rated data  
rated cross-section  $4 \text{ mm}^2$   
rated current 41A  
rated voltage 400V



GENERAL TOLERANCE: DIN ISO 2768-m		91733/5 21.03.17 MA_J	01	Modification	Cat. no.:
Max. nos.	RoHS COMPLIANT				
				Date	Name
				Drawn	03.11.2006 SHI_S
				Responsible	MA_J
Scale: 4/1				Checked	21.03.2017 ZHOU_N
Supersedes: .				Approved	XU_S
				Product file:	WGK 4

Weidmüller

C 39513 03

Drawing no. 01 of 01 sheets

WGK 4...  
Durchf\_rungsklemme  
Feed-Through Terminal