

IE- C		5	A	S	4	U	G	1000	A21	A40	-Y										
C	Copper	5	Cat.5	A	AWG 22/1	S	System cabel	4	4 wires	U	PUR	Y	Yellow	1000	Length in dm (1000 = 100m)	A20	RJ45 IP20 plug AWG22 metal	A20	RJ45 IP20 plug AWG22 metal	-Y	Yellow sleeve
...		6	Cat.6	B	AWG 23/1	L	System cabel	8	8 wires	V	PVC	W	White	025C	Length in cm (025C = 25 cm)	A21	RJ45 plug AWG22 IDC V1 metal	A21	RJ45 plug AWG22 IDC V1 metal	-W	White sleeve
		S	Control cable	C	AWG 24/1	H	Hybrid	A	10 wires	E	PE	O	Orange	...		A24	RJ45 plug AWG22 IDC V4 plastic	A24	RJ45 plug AWG22 IDC V4 plastic	-O	Orange sleeve
				D	AWG 22/7	D	Dragchain			L	LSZH	R	Red			A25	RJ45 plug AWG22 IDC V5 metal	A25	RJ45 plug AWG22 IDC V5 metal	-R	Red sleeve
				E	AWG 26/7	T	Torsion			R	Radox	B	Blue			A2D	RJ45 IP20 plug AWG 22 metal with dust cab	A2D	RJ45 IP20 plug AWG 22 metal with dust cab	-B	Blue sleeve
				F	AWG 27/7	P	Patch cabel			W	Radox (RW)	G	Green			A2E	RJ45 plug AWG22 IDC V14 metal	A2E	RJ45 plug AWG22 IDC V14 metal	-G	Green sleeve
				H	AWG 26/19	B	Rail cord			F	FRNC	T	Teal			A30	RJ45 IP20 plug AWG22-27 metal plug	A30	RJ45 IP20 plug AWG22-27 metal plug	-E	Black sleeve
				I	AWG 22/19	...				H	HFFR	E	Black			A40	RJ45 IP20 plug AWG24- AWG27	A40	RJ45 IP20 plug AWG24- AWG27	-D	Grey sleeve
				P	1,5 mm ²							D	Grey			A41	RJ45 plug AWG24 (Crimp) V1 metal	A41	RJ45 plug AWG24 (Crimp) V1 metal	-X	no choice
				...								S	Silvergrey			A44	RJ45 plug AWG24 (Crimp) V4 plastic	A44	RJ45 plug AWG24 (Crimp) V4 plastic	-X	0° standard
												M	Magenta			A45	RJ45 plug AWG24 (Crimp) V5 metal	A45	RJ45 plug AWG24 (Crimp) V5 metal	-1	45°
												...				A5A	RJ45 socket IDC SteadyTec A-coded	A5A	RJ45 socket IDC SteadyTec A-coded	-2	90°
																A5B	RJ45 socket IDC SteadyTec B-coded	A5B	RJ45 socket IDC SteadyTec B-coded	-3	135°
																A5P	RJ45 socket IDC SteadyTec P-coded	A5P	RJ45 socket IDC SteadyTec P-coded	-4	180°
																A60	RJ45 IP20 plug AWG22	A60	RJ45 IP20 plug AWG22	-5	225°
																AQE	Hybrid plug Q10 V14 metal	AQE	Hybrid plug Q10 V14 metal	-6	270°
																B2E	RJ45 plug AWG22 IDC V14 metal moulded	B2E	RJ45 plug AWG22 IDC V14 metal moulded	-7	315°
																B41	RJ45 plug AWG24 (Crimp) V1 plastic	B41	RJ45 plug AWG24 (Crimp) V1 plastic	-8	255°
																C20	Crossover RJ45 IP20 plug AWG22	C20	Crossover RJ45 IP20 plug AWG22	-9	210°
																C40	Crossover RJ45 IP20 plug AWG24-AWG27	C40	Crossover RJ45 IP20 plug AWG24-AWG27	-U	RJ45 angeled up
																M40	RJ45 IP20 plug AWG24- AWG27 + marking sleeve	M40	RJ45 IP20 plug AWG24- AWG27 + marking sleeve	-D	RJ45 angeled down
																MBS	M12 bulkhead socket straight backpanel mounting	MBS	M12 bulkhead socket straight backpanel mounting	-L	RJ45 angeled left
																MCA	M12 plug angled	MCA	M12 plug angled	-R	RJ45 angeled right
																MCF	M12 bulkhead plug straight front mounting	MCF	M12 bulkhead plug straight front mounting	-UD	RJ45 angeled up / RJ45 angeled down
																MCH	M12 bulkhead plug straight backpanel mounting	MCH	M12 bulkhead plug straight backpanel mounting	-RL	RJ45 angeled right / RJ45 angeled left
																MCS	M12 plug straight	MCS	M12 plug straight	...	
																MSA	M12 socket angled	MSA	M12 socket angled		
																MSF	M12 bulkhead socket straight front mounting	MSF	M12 bulkhead socket straight front mounting		
																MSS	M12 socket straight	MSS	M12 socket straight		
																P21	RJ45 plug AWG22 V1 plastic moulded IDC	P21	RJ45 plug AWG22 V1 plastic moulded IDC		
																P41	RJ45 plug AWG24 V1 plastic moulded crimp	P41	RJ45 plug AWG24 V1 plastic moulded crimp		
																S21	RJ45 plug AWG22 V1 plastic	S21	RJ45 plug AWG22 V1 plastic		
																S41	RJ45 plug AWG24 V1 plastic	S41	RJ45 plug AWG24 V1 plastic		
																V40	RJ45 IP20 plug angled 90° AWG24- AWG27 + marking sleeve	V40	RJ45 IP20 plug angled 90° AWG24- AWG27 + marking sleeve		
																VAP	Push Pull Power plug AIDA	VAP	Push Pull Power plug AIDA		
																W30	RJ45 IP20 plug angled (metal) AWG22 + marking sleeve	W30	RJ45 IP20 plug angled (metal) AWG22 + marking sleeve		
																W40	RJ45 IP20 plug angled 270° + marking sleeve	W40	RJ45 IP20 plug angled 270° + marking sleeve		
																X40	Crossover RJ45 IP20 plug + marking sleeve	X40	Crossover RJ45 IP20 plug + marking sleeve		
																XCA	M12 X-Code plug angled	XCA	M12 X-Code plug angled		
																XCF	M12 X-Code bulkhead plug straight front mounting	XCF	M12 X-Code bulkhead plug straight front mounting		
																XCH	M12 X-Code bulkhead plug straight backpanel mounting	XCH	M12 X-Code bulkhead plug straight backpanel mounting		
																XCS	M12 X-Code plug straight	XCS	M12 X-Code plug straight		
																XSF	M12 X-Code bulkhead socket straight front mounting	XSF	M12 X-Code bulkhead socket straight front mounting		
																XSH	M12 X-Code bulkhead socket straight backpanel mounting	XSH	M12 X-Code bulkhead socket straight backpanel mounting		
																XSS	M12 X-Code socket straight	XSS	M12 X-Code socket straight		
																XXX	open end, no plug	XXX	open end, no plug		
																...					

straight plug

M12 plug angled

RJ45 plug angled