





Technical drawing of a cable gland (PG9) showing dimensions and labels:

- PG9**: Cable gland type.
- M12x1**: Thread specification.
- O-Ring FPM**: Fluoropolymer O-ring.
- SW 19**: Hex key size.
- O-Ring NBR**: Nitrile O-ring.
- Dimensions**:
 - 18**: Height of the main body.
 - 20,5**: Total height.
 - Ø0,8**: Cable diameter.
 - D2**: Inner diameter of the gland.
 - D1**: Outer diameter of the gland.
 - L**: Length of the gland.
- A**: Arrow indicating the direction of force or assembly.



Order no.:	Description:	Pole	Length L:	D1	D2
2421920000	SAIE-M12B-4-H5.5TL-PG9	4	5,5mm	Ø5,0	Ø1,6
2421980000	SAIE-M12B-5-H5.5TL-PG9	5			
2422040000	SAIE-M12B-8-H5.5TL-PG9	8		Ø5,5	Ø1,4
2421950000	SAIE-M12B-4-H12TL-PG9	4	12mm	Ø5,0	Ø1,6
2422010000	SAIE-M12B-5-H12TL-PG9	5			
2422070000	SAIE-M12B-8-H12TL-PG9	8		Ø5,5	Ø1,4