









WEIDMÜLLER reserves the right to the FOR PATENTS, utility models or designs.
WEIDMÜLLER INTERFACE GmbH & Co. KG
WIEDERHERGABE SOWIE VERVIelfÄLTIGUNG DIESES DOKUMENTS, VERWERTUNG UND MITTELUNG SEINES INHALTS SIND VERBOTEN, SOWEIT NICHT AUSDRÜCKLICH GESTÄTTET.
ZUMIDRHANDLUNGEN VERPFLICHTET ZU SCHADENERSATZ. ALLE RECHTE EINER DEN FALL DER PATENT-, GEBRAUCHSMUSTER- ODER GESCHMACKSMUSTERINRAUMUNG VORBEHALTEN.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMÜLLER EXPRESSLY RESERVES THE RIGHT TO THE FOR PATENTS, utility models or designs.



Additional product documents				1.						Tolerances: ISO 2768-mK				
				2.										
					Date	Name		Weidmüller						
					Drawn	27/11/2019								wes0383
					Checked	27/02/2020		wes0383						
					Criterion for print				Description:					
					1 : 1		A3		PV 218S0F0C15V0O3TXPX15PFWW					
					Customer:				Drawing-No / Material-No: 8000057083 drw Index 1Sheet 1 / 2					
					WEIDMÜLLER, S.A.									
1	Replace obseleted components	20/10/2023	wes0212	Customer-No: 104000066										
0		27/11/2019	wes0383											
Index	Brief Description	Date	Name					Customer Description:						