


WIEDERGABE SOWIE VERVIÄLTIGUNG DIESER DOKUMENTS, VERWERTUNG UND MITTELUNG SEINER INHALTS SIND VERBOTEN, SOWEIT NICHT AUSDRÜCKLICH GESTÄTET.
ZUMIDRHANDLUNGEN VERPFLICHTEN ZU SCHADENERSATZ. ALLE RECHTE FÜR DEN FALL DER PATENT-, GEBRAUCHSMUSTER- ODER GESCHMACKSMUSTERINTEGRATION VORBEHALTEN.
THE REPRODUCTION, DISTRIBUTION AND UTILISATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMÜLLER EXCLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS.
WIEDERMÜLLER INTERFACE GmbH & Co. KG



Additional product documents				1.		Tolerances: ISO 2768-mK			
				2.					
				Date		Name			
				Drawn		22/07/2019 wes0283			
				Checked					
				Criterion for print				Description:	
				1 : 1		A3		PV 216S0F0C15V0O1TXPX15PFWM	
				Customer:				Drawing-No / Material-No: 8000057078 drw Index 0Sheet 1 / 4	
				WEIDMÜLLER, S.A					
				Customer-No:					
0		22/07/2019	wes0283						
Index	Brief Description	Date	Name					Customer Description:	

PV 216S0F0C15V0O1TXPX15PFWW