

Field Wiring Solutions

## Core Portfolio

Heavy Duty Connectors / Industrial Ethernet /  
Sensor Actor Interfaces



**Weidmüller** 



## Field Wiring Solutions

### CORE PORTFOLIO

As a planning engineer, do you want to select products easily and receive them quickly? From a partner you can rely on? Then plan with the product portfolio from Weidmüller in the future. Our core portfolio is always on stock, carefully selected and the portfolio consists of more than 1,500 items to fully cover your standard needs.



More information on our Website:  
[www.weidmueller.com/fieldwiring](http://www.weidmueller.com/fieldwiring)

# Heavy Duty Connectors



Type	Order No.
HDC 04A ALU	1497600000
HDC 04A SLU 1M20G	1788830000
HDC 04A TOLU 1M20G	1788820000
HDC 06B ADLU	1202500000
HDC 06B ALU	1202100000
HDC 06B ALU N	2488560000
HDC 06B SDLU 2M20G	1788170000
HDC 06B TSLU 1M20G	1788100000
HDC 10B ABU	1205000000
HDC 10B ABU N	2488580000
HDC 10B ADLU	1206500000
HDC 10B TSLU 1M25G	1787580000
HDC 16A ALU	1664920000
HDC 16B ABU	1208600000
HDC 16B ABU N	2488590000
HDC 16B ADLU	1210100000
HDC 16B ALU	1209700000
HDC 16B DDDQ 4B0	1665260000
HDC 16B TSBU 1M25G	1788180000
HDC 24B ABU	1212400000
HDC 24B ABU N	2488600000
HDC 24B ADLU	1214300000
HDC 24B SBU 1M25G	1901150000
HDC 24B TSBU 1M32G	1787750000
HDC 40D TSBU 1M32G	1787000000
HDC 64D TSBU 1M40G	1809630000
HDC HA 10 FS	1650620000
HDC HA 10 MS	1650610000
HDC HA 16 FS	1650780000
HDC HA 16 FT	1896800000
HDC HA 16 MS	1650770000
HDC HA 16 MT	1896830000
HDC HA 3 FS	1498200000
HDC HA 3 MS	1498100000
HDC HA 4 FS	1498400000
HDC HA 4 MS	1498300000
HDC HD 40 FC	1601730000
HDC HD 40 MC	1601710000
HDC HDD 42 FC	1651180000
HDC HDD 42 MC	1651170000
HDC HE 06 N FQT	2666920000
HDC HE 06 N MQT	2666910000
HDC HE 10 FP	1873540000
HDC HE 10 FS	1204100000
HDC HE 10 MP	1873550000
HDC HE 10 MS	1203900000
HDC HE 10 N FQT	2666930000
HDC HE 10 N MQT	2666940000
HDC HE 16 FP	1873560000
HDC HE 16 FS	1207700000
HDC HE 16 MP	1873570000
HDC HE 16 MS	1207500000
HDC HE 16 N FQT	2666950000
HDC HE 16 N MQT	2666970000
HDC HE 24 FP	1873580000
HDC HE 24 FS	1211300000
HDC HE 24 MP	1873590000
HDC HE 24 MS	1211100000
HDC HE 24 N MQT	2667010000
HDC HE 24 N FQT	2666990000
HDC HE 6 FP	1873520000
HDC HE 6 FS	1200200000
HDC HE 6 MP	1873530000
HDC HE 6 MS	1200000000
HDC HEE 32 FC	1826800000
HDC HEE 32 MC	1826790000
HDC HEE 46 FC	1826780000

Type	Order No.
HDC HEE 46 MC	1826770000
HDC HQ 5 FC	1912460000
HDC HQ 5 MC	1912440000
HDC HSB 6 FS	1498900000
HDC HSB 6 MS	1498700000
HDC MBUS 2 FC	1429020000
HDC MBUS 2 MC	1428990000
HDC MDU	1429040000
HDC MF 10B AC	1428960000
HDC MF 10B CA	1428980000
HDC MF 16B AD	1429010000
HDC MF 16B DA	1429030000
HDC MF 24B AF	1429050000
HDC MF 24B FA	1429070000
HDC MF 6B AB	1428920000
HDC MF 6B BA	1428940000
HDC MHD 12 FP	2748470000
HDC MHD 12 MP	2748460000
HDC MHD 36 FC	1428870000
HDC MHD 36 MC	1428860000
HDC MHE 20 FC	1428930000
HDC MHE 20 MC	1428910000
HDC MHE 6 FC	1429370000
HDC MHE 6 FP	2748430000
HDC MHE 6 MC	1429360000
HDC MHE 6 MP	2748420000
HDC MHE 8 FP	2748450000
HDC MHE 8 MP	2748440000
HDC MHP 100 FAS	2748290000
HDC MHP 100 FC	1429080000
HDC MHP 100 MAS	2748280000
HDC MHP 100 MC	1429060000
HDC MHP 200 FAS	2748250000
HDC MHP 200 MAS	2748240000
HDC MHP 200 PE FAS	2748270000
HDC MHP 200 PE MAS	2748260000
HDC MHP 70 FAS	2748310000
HDC MHP 70 MAS	2748300000
HDC MHP100 F 16	1435810000
HDC MHP100 F 25	1435820000
HDC MHP100 M 16	1435760000
HDC MHP100 M 25	1435770000
HDC MHX 2 FP	2772830000
HDC MHX 2 MP	2772820000
HDC MHX 3 FP	2772790000
HDC MHX 3 MP	2772780000
HDC MHX 4P FC	1428970000
HDC MHX 4P FP	2772810000
HDC MHX 4P MC	1428950000
HDC MHX 4P MP	2772800000
HDC-C-HD-BM0.14-0.37AG	1651570000
HDC-C-HD-BM0.5AG	1651580000
HDC-C-HD-BM0.75-1.00AG	1601760000
HDC-C-HD-BM1.5AG	1651600000
HDC-C-HD-SM0.14-0.37AG	1651520000
HDC-C-HD-SM0.5AG	1651530000
HDC-C-HD-SM0.75-1.00AG	1601750000
HDC-C-HD-SM1.5AG	1651550000
HDC-C-HE-BM1.5AG	1201300000
HDC-C-HE-BM2.5AG	1201400000
HDC-C-HE-SM1.5AG	1200700000
HDC-C-HE-SM2.5AG	1200800000
HDC-KIT-HE 10.110	1712510000
HDC-KIT-HE 16.120	1712520000
HDC-KIT-HE 24.130	1712530000
DSTV COBU5	1471500000
DSTV COST4	1471300000

# Industrial Ethernet

Type	Order No.
IE-PS-V14M-RJ45-FH-P	1012170000
IE-BSS-V14M-RJ45-C	1012310000
IE-FCM-RJ45-C	1018790000
IE-FCM-RJ45-FJ-A	1018810000
IE-FCM-RJ45-FJ-P	1018830000
IE-FCM-USB-A	1018840000
IE-BI-USB-A	1019570000
IE-C5DD4UG0005MCSMCS-E	1025950005
IE-C5DD4UG0010MCSMCS-E	1025950010
IE-C5DD4UG0050MCSMCS-E	1025950050
IE-C5DD4UG0100MCSMCS-E	1025950100
IE-BSS-V14M-HYB-10P-FJ	1072900000
IE-PS-V14M-HYB-10P	1072910000
IE-BSS-V14M-RJ45-FJ-P	1085260000
IE-PS-RJ45-FH-BK-A	1132040000
IE-PS-RJ45-FH-BK-B	1132050000
IE-PS-RJ45-FH-BK-P	1132060000
IE-C6FP8LD0002M40M40-D	1165940002
IE-C6FP8LD0005M40M40-D	1165940005
IE-C6FP8LD0010M40M40-D	1165940010
IE-C6FP8LD0015M40M40-D	1165940015
IE-C6FP8LD0020M40M40-D	1165940020
IE-C6FP8LD0030M40M40-D	1165940030
IE-C6FP8LD0050M40M40-D	1165940050
IE-C6FP8LD0100M40M40-D	1165940100
IE-FCM-USB-AB	1222550000

Type	Order No.
IE-C6FP8LD0005M40W40-D	1233160005
IE-C6FP8LD0005M40V40-D	1248280005
IE-FCM-USB-3.0-A	1427960000
IE-FC-SFP-KNOB	1450510000
IE-FC-SP-PWB/2ST	1450550000
IE-FCI-PWB-DE	1450730000
IE-BI-USB-3.0-A	1487920000
IE-PS-RJ45-FH-90-A-1.1	1518080000
IE-PS-RJ45-FH-90-B-1.1	1518090000
IE-PS-RJ45-FH-90-P-1.6	1518100000
IE-BI-RJ45-C	1962840000
IE-PS-V04P-RJ45-FH	1963160000
IE-PS-V05M-RJ45-FH	1963200000
IE-BS-V04P-RJ45-C	1963490000
IE-BS-V05M-RJ45-C	1963510000
IE-PS-RJ45-TH-BK	1963590000
IE-PS-RJ45-FH-BK	1963600000
IE-PS-RJ45-FH-90-A-1.6	1992870000
IE-PS-RJ45-FH-90-B-1.6	1992890000
IE-PS-VAPM-5P-2.5	2465440000
IE-BSS-VAPM-24V	2493480000
IE-XM-RJ45/DC	8808360000
IE-P63	8813110000
IE-P70	8813120000
IE-XM-RJ45/RJ45	8879050000
IE-M12-ADAP S	8901620000
IE-M12-ADAP A	8901630000
IE-M12-COUP	8901640000
IE-TO-RJ45-C	8946920000
IE-TO-RJ45-FJ-A	8946930000
IE-TO-RJ45-FJ-B	8946940000
IE-TO-SCD-MM	8946970000
IE-C6FP8LG0005M40M40-G	1251590005
IE-C6FP8LG0010M40M40-G	1251590010
IE-C6FP8LG0015M40M40-G	1251590015
IE-C6FP8LG0020M40M40-G	1251590020
IE-C6FP8LG0025M40M40-G	1251590025
IE-C6FP8LG0030M40M40-G	1251590030
IE-C6FP8LG0040M40M40-G	1251590040
IE-C6FP8LG0050M40M40-G	1251590050
IE-C6FP8LG0100M40M40-G	1251590100
IE-C6FP8LG0150M40M40-G	1251590150
IE-C6FP8LG0200M40M40-G	1251590200
IE-C6FP8LG0250M40M40-G	1251590250
IE-C6FP8LG0500M40M40-G	1251590500



# Sensor Actor Interfaces

Type	Order No.
RS PB-DP T	8800040000
SAI-06L-VP12-3A-M08L-PNP	1828730000
SAI-06L-VPFC-3A-M08L-PNP-05U02	1828700000
SAI-08L-VP12-3A-M08L-PNP	1871680000
SAI-08L-VPFC-3A-M08L-PNP-05U03	1828680000
SAI-08L-VPFC-3A-M08L-PNP-10U03	1828670000
SAI-4-F 4P PUR 10M	9456200000
SAI-4-F 4P PUR 5M	9456190000
SAI-4-F 5P PUR 5M	9456330000
SAI-4-M 5P M12	1701230000
SAI-4-M 5P M12 1:1	1806010000
SAI-4-M-4P-M12-SVV	1431490000
SAI-4-M-MVV-M12 1:1	2009620000
SAI-6-M 5P M12	1701240000
SAI-8-F 4P PUR 10M	9456760000
SAI-8-F 4P PUR 5M	9456750000
SAI-8-F 5P PUR 10M	9456900000
SAI-8-F 5P PUR 5M	9456890000
SAI-8-M 4P M12	1705940000
SAI-8-M 5P M12	1701250000
SAI-8-S 5P FC	1848040000
SAIBGI-P-4A-2.9/5.1-M12	1781540001
SAIBGS-M-4A-6/8-M12	8426220000
SAIBGS-M-4D-6/8-M12	1892130000
SAIBGS-M-5A-6/8-M12	1784750000
SAIBGS-P-3A-3.5/5-M8	1803860000
SAIBGS-P-3A-3.5/5-M8	1803870000
SAIBGS-P-4A-3.5/5-M8	1803880000
SAIBGS-P-4A-4/6-M12	9457240000
SAIBGS-P-4A-6/8-M12	1807230000
SAIBGS-P-5A-4/6-M12	9457250000

Type	Order No.
SAIBGS-P-5A-6/8-M12	1807250000
SAIBGS-P-8A-6/8-M12	1836960000
SAIBM 5/8S M12 5P B-COD	1784780000
SAIB-M23-19P-AN-10M	1818141000
SAIB-M23-19P-AN-5,0M	1818140500
SAIBWS-P-4A-4/6-M12	9457700000
SAIL-M12BG-4-10U	9457731000
SAIL-M12BG-4-5.0U	9457730500
SAIL-M12BG-5-5.0U	9457910500
SAIL-M12BW-4-10U	9457741000
SAIL-M12BW-4-5.0U	9457740500
SAIL-M8BG-3-10U	9457451000
SAIL-M8BG-3-5.0U	9457450500
SAIL-M8BG-4-10U	9457851000
SAIL-M8BG-4-5.0U	9457850500
SAIL-M8BW-3-5.0U	9457380500
SAISGI-P-3A-3.2/5.4-M8	1784040001
SAISGI-P-4A-2.9/5.1-M12	1781550001
SAISGS-M-4A-6/8-M12	9456640000
SAISGS-M-4D-6/8-M12	1892120000
SAISGS-M-5A-6/8-M12	1784740000
SAISGS-P-4A-3.5/5-M8	1803850000
SAISGS-P-4A-4/6-M12	9457550000
SAISGS-P-4A-6/8-M12	1807340000
SAISGS-P-5A-4/6-M12	9456940000
SAISGS-P-5A-6/8-M12	1807350000
SAISGZ-M-4D-6/8-M12	1892120001
SAISWS-P-5A-4/6-M12	9456950000
SAI-Y-4-4/2-4 M12/8	1783420000
SCREWTY- M12	1900000000
SCREWTY SET-DM	1920000000



## **Weidmüller – Your partner in Smart Industrial Connectivity**

As experienced experts we support our customers and partners around the world with products, solutions and services in the industrial environment of power, signal and data. We are at home in their industries and markets and know the technological challenges of tomorrow. We are therefore continuously developing innovative, sustainable and useful solutions for their individual needs. Together we set standards in Smart Industrial Connectivity.

We cannot guarantee that there are no mistakes in the publications or software provided by us to the customer for the purpose of making orders. We try our best to quickly correct errors in our printed media.

All orders are based on our general terms of delivery, which can be reviewed on the websites of our group companies where you place your order. On demand we can also send the general terms of delivery to you.

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
32758 Detmold, Germany  
T +49 5231 14-0  
F +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

Personal support can  
be found on our website:  
[www.weidmueller.com/contact](http://www.weidmueller.com/contact)

Made in Germany

04/2025