

CSP file change-log of new features, bug fixes and new supported modules of the u-remote field bus coupler: 2625010000 UR20-FBC-CC**Version: 20260312****Release date: March, 2026**

New version (identical to 20250708)

Version: 20250708**Release date: July, 2025****New supported modules:**

- 2819690000 - UR20-4COM-IO-LINK-V2
- 3096630000 - SAI-AU-M8-SB-8DO-2A-V2
- 3096500000 - SAI-AU-M8-SB-8DI-V2
- 3096510000 - SAI-AU-M8-SB-8DIO-V2
- 3096490000 - SAI-AU-M12-SB-8DO-2A-V2
- 3096470000 - SAI-AU-M12-SB-8DI-V2
- 3096480000 - SAI-AU-M12-SB-8DIO-V2

Version: 20250211**Release date: February, 2025**

New version (identical to 20241106)

Version: 20241106**Release date: November, 2024****New supported modules:**

- 2920830000 - UR20-3EM-400V-AC-CT1A
- 2920840000 - UR20-3EM-400V-AC-CT5A
- 2920850000 - UR20-3EM-400V-AC-RC
- 2920860000 - UR20-3EM-400V-AC-333MV
- 2489840000 - UR20-1COM-CAN

Version: 20240611**Release date: June 2024****New supported modules:**

- 3036960000 - UR20-2PWM-PN-0.5A-V2
- 3036950000 - UR20-2PWM-PN-2A-V2

Version: 20231116**November 2023****New supported modules:**

- 2489840000 - UR20-1COM-CANOPEN

Version: 20220713**August 2022****New supported modules:**

- 2697910000 UR20-2PWM-I-2.5A-2DI-P

Version: 20220314**April 2022****New supported modules:**

- 2826800000 UR20-1COM-232-485-422-V2

Version: 20210121**February 2021****New feature:**

- Support of new version of UR20-2AI-SG-24-DIAG with MX file 001051.110 which is calibrated for an extended range of sensor sensitivity up to 960mV/V. **CAUTION:** Modules with MX file versions below 001501.110 are calibrated for a maximum sensor sensitivity range of 30mV/V and will return no valid measurement values if used outside this range!

Bug fix:

- Minor changes in value ranges for modules.

New supported modules:

- 2705620000 UR20-2AI-UI-16
- 2566090000 UR20-2AI-UI-16-DIAG

- 2705630000 UR20-2AO-UI-16
- 2566100000 UR20-2AO-UI-16-DIAG

Version**Release date: September 2020**

- First released version will not be longer supported.