



Ref. Certif. No.

NL-80241

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

terminal block for copper conductors

Name and address of the applicant

Weidmüller Interface GmbH & Co. KG
Klingenbergsstrasse 16 / 26
32758 Detmold
Germany

Name and address of the manufacturer

Weidmüller Interface GmbH & Co. KG
Klingenbergsstrasse 16 / 26
32758 Detmold
Germany

Name and address of the factory

Weidmüller Interface GmbH & Co. KG
Klingenbergsstrasse 16 / 26
32758 Detmold
Germany Additional information on page 2

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

500 V, 6 kV, 41 A, 6 mm², service life 250 cycles

Trademark / Brand (if any)

Weidmüller

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

WTL 6 STB

Additional information (if necessary may also be reported on page 2)

 Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60947-7-1:2009

As shown in the Test Report Ref. No. which forms part of this Certificate

2264169.50

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
Arnhem, 6825 MJ
Netherlands

Date: 2023-05-11


Signature: H.R.M. Barends




Ref. Certif. No.

NL-80241

Additional factory

WEIDMÜLLER INTERFACE ROMANIA SRL
Strada 66
437345 Tautii Magheraus
Romania

Weidmuller Lanskroun, s.r.o.
Dobrovskeho 1115
56301 Lanskroun
Czech Republic

EWE s.r.o.
Trebovska 570
562 03 Usti Nad Orlici
Czech Republic

Weidmüller Interface (Suzhou) Co. Ltd.
No. 58 Shilin Road
215151 Suzhou Jiangsu
China

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
Arnhem, 6825 MJ
Netherlands



Date: 2023-05-11

Signature: H.R.M. Barends