



Product Service

CERTIFICATE

No. B 033299 0443 Rev. 00

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergstr. 16
32758 Detmold
GERMANY

Certification Mark:

**Product:**

Power supply

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.

Test report no.:

6821019007901

Valid until:

2024-03-21

Date, 2019-03-22

(Yager Bi)



Product Service

CERTIFICATE

No. B 033299 0443 Rev. 00

Model(s): PRO INSTA 30W 12V 2.6A, PRO INSTA 30W 24V 1.3A

Brand Name: Weidmüller

Weidmüller 

Parameters:

Rated Input : 100-240VAC, 50-60Hz, 1.0-0.5A; or 120-340VDC, 0.5-0.2A

Rated Output : 12VDC/2.6A (for model: PRO INSTA 30W 12V 2.6A),
24VDC/1.3A (for model: PRO INSTA 30W 24V 1.3A)

Protection Class : II

Degree of Protection : IPX0

Remarks :

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Maximum operating temperature is 70°C.
- This power supply contains output with hazardous power source, when installing into end system, care must be taken that the output and associated wire(s) may not be touched.
- Built-in type equipment, suitable enclosure and type of supply connection should be provided by end system.

Tested according to: EN 62368-1:2014/A11:2017

Production 069022

Facility(ies):