

SKMU ロックナットの難燃性グレード 誤記修正のお知らせ

拝啓

貴社にはご清栄のこととお慶び申し上げます。
平素は格別のお引き立てを賜り、誠にありがとうございます。

この度、樹脂製ロックナットの SKMU シリーズの製品仕様におきまして web 上のデータやカタログ及び data sheet に記載があります難燃性グレードに誤記が見つかり修正を行う事となりました。

現在該当製品をご利用中のお客様には、ご面倒をおかけいたしますが、何卒ご理解のほどよろしく
お願い致します。

敬具

■ 変更内容

難燃性(UL 94)の表記の訂正 V2 を HB に修正します。

※その他の材質・機能性等に関する変更はございません。

旧 (誤記の製品仕様)	新しい材料データ																																						
 <p>Lock nuts with collar for preventing enclosure damage on installation. These are used to secure plastic cable glands and blanking plugs - recommended for Ex e and Ex i plastic cable glands.</p>	  																																						
<p>Technical data</p> <table border="1"> <tr> <td>Material / Colour</td> <td>Polyamid 6 (PA6 - GF30) / Deep black / RAL 9005</td> </tr> <tr> <td>Temperature range</td> <td>-40 °C...100 °C</td> </tr> <tr> <td>Flammability rating</td> <td>V2</td> </tr> <tr> <td>Note</td> <td>Accessories for Ex cable glands are not subject to approval.</td> </tr> </table>	Material / Colour	Polyamid 6 (PA6 - GF30) / Deep black / RAL 9005	Temperature range	-40 °C...100 °C	Flammability rating	V2	Note	Accessories for Ex cable glands are not subject to approval.	<table border="1"> <tr> <td colspan="2">General ordering data</td> </tr> <tr> <td colspan="2">Dimensions and weights</td> </tr> <tr> <td colspan="2">General information</td> </tr> <tr> <td>Material</td> <td>Polyamid 6 (PA6 - GF30)</td> </tr> <tr> <td>Cable glands</td> <td>metric</td> </tr> <tr> <td>External thread</td> <td>M 25</td> </tr> <tr> <td>Pitch of thread</td> <td>1.5 mm</td> </tr> <tr> <td>Length of thread</td> <td>6 mm</td> </tr> <tr> <td>AF size 1</td> <td>32 mm</td> </tr> <tr> <td>Operating temperature range, min.</td> <td>-40 °C</td> </tr> <tr> <td>Operating temperature range, max.</td> <td>100 °C</td> </tr> <tr> <td>Thickness</td> <td>6 mm</td> </tr> <tr> <td>UL 94 flammability rating</td> <td>HB</td> </tr> <tr> <td>Internal thread</td> <td>M 25</td> </tr> <tr> <td>Halogen</td> <td>No</td> </tr> </table>	General ordering data		Dimensions and weights		General information		Material	Polyamid 6 (PA6 - GF30)	Cable glands	metric	External thread	M 25	Pitch of thread	1.5 mm	Length of thread	6 mm	AF size 1	32 mm	Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C	Thickness	6 mm	UL 94 flammability rating	HB	Internal thread	M 25	Halogen	No
Material / Colour	Polyamid 6 (PA6 - GF30) / Deep black / RAL 9005																																						
Temperature range	-40 °C...100 °C																																						
Flammability rating	V2																																						
Note	Accessories for Ex cable glands are not subject to approval.																																						
General ordering data																																							
Dimensions and weights																																							
General information																																							
Material	Polyamid 6 (PA6 - GF30)																																						
Cable glands	metric																																						
External thread	M 25																																						
Pitch of thread	1.5 mm																																						
Length of thread	6 mm																																						
AF size 1	32 mm																																						
Operating temperature range, min.	-40 °C																																						
Operating temperature range, max.	100 °C																																						
Thickness	6 mm																																						
UL 94 flammability rating	HB																																						
Internal thread	M 25																																						
Halogen	No																																						

■ 変更時期

本お知らせは、仕様書の誤記の内容修正であるため web data や data sheet の内容は既に変更(修正)が完了しています。

■ 対象製品

対象製品の品番、型式につきましては、下記の通りとなります。

対象製品			
グレー色		黒色	
製品品名	対象型番	製品品名	対象型番
SKMU M12 - K GR	1772440000	SKMU M12 K SW	1806540000
SKMU M16 - K GR	1772450000	SKMU M16 K SW	1736920000
SKMU M20 - K GR	1772460000	SKMU M20 K SW	1736930000
SKMU M25 - K GR	1772470000	SKMU M25 K SW	1736940000
SKMU M32 - K GR	1772480000	SKMU M32 K SW	1736950000
SKMU M40 - K GR	1772490000	SKMU M40 K SW	1736960000
SKMU M50 - K GR	1772500000	SKMU M50 K SW	1736970000
SKMU M63 - K GR	1772510000	SKMU M63 K SW	1736980000
SKMU PG 13,5-K GR	1697470000	SKMU PG11-K SW	1719120000
SKMU PG11-K GR	1697460000	SKMU PG13,5-K SW	1719130000
SKMU PG16-K GR	1697480000	SKMU PG16-K SW	1719140000
SKMU PG21-K GR	1698220000	SKMU PG21-K SW	1719150000
SKMU PG29-K GR	1698230000	SKMU PG29-K SW	1719160000
SKMU PG36-K GR	1698240000	SKMU PG36-K SW	1719170000
SKMU PG42-K GR	1698250000	SKMU PG42-K SW	1719180000
SKMU PG48-K GR	1719090000	SKMU PG48-K SW	1719190000
SKMU PG7-K GR	1697440000	SKMU PG7-K SW	1719100000
SKMU PG9-K GR	1697450000	SKMU PG9-K SW	1719110000

今後とも弊社製品をご愛用いただけますようお願い致します。
 ご不明点がございましたら下記までお問い合わせください。

【本件に関するお問い合わせ先】

日本ワイドミュラー株式会社 技術部
 〒140-0002 東京都品川区東品川 2-2-8 スフィアタワー天王洲
 TEL: 03-6711-5302 FAX : 03-6711-5333
 E-mail: info@weidmuller.co.jp
<http://www.weidmuller.co.jp>