



Product Service

CERTIFICATE

No. B 033299 0515 Rev. 00

Model(s): PRO ECO3 480W 24V 20A

Brand Name: Weidmüller

Weidmüller 

Parameters:

Rated Input : 3 x 400-500VAC, 50/60Hz, 3 x 1.5-1.2A

or 450-500VDC, 1.3-1.1A

Rated Output : 24VDC, 20A

Protection Class : I

Degree of Protection : IP20

Remarks :

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Built-in type equipment, suitable enclosure and type of supply connection should be provided by end system.
- Refer to installation instruction from manufacturer for details of loading condition and operating ambient temperature.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- When installing the power supply, keep min. 5cm distance for bottom openings for ventilation.

Tested according to: EN 62368-1:2014/A11:2017

Production 057937

Facility(ies):

TÜV SÜD
ZERTIFIKAT ◆ CERTIFICATE ◆ 認證證書 ◆ CERTIFICADO ◆ CERTIFICAT