



Product Service

CERTIFICATE

No. B 033299 0503 Rev. 00

Model(s): PRO ECO3 960W 24V 40A

Brand Name: Weidmüller

Weidmüller 

Parameters:

Rated Input : 3 x 400-500VAC, 50/60Hz, 3 x 3.4-3.2A
or 450-500VDC, 2.5-2.3A

Rated Output : 24VDC, 40A

Construction : Built-in

Protection Class : I

Degree of Protection : IP20

Remarks :

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Built-in type equipment, suitable enclosure and type of supply connection should be provided by end system.
- The output is hazardous power source, when installing the equipment into end system, care must be taken that the output and associated wire(s) should not be touched.
- Refer to installation instruction from manufacturer for details of loading condition and operating ambient temperature.
- Clearance was evaluated for operating altitude up to 5000m above sea level.

Tested according to: EN 62368-1:2014/A11:2017

Production 057937

Facility(ies):