






WEITERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
Zu widerhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksuntereintragung vorbehalten.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. ALL RIGHTS RESERVED IN THE EVENT OF THE GRANT OF A PATENT, UTILITY MODEL OR DESIGN.

MASSE OHNE TOLERANZ SIND KEINE PRUEFMASSE
DIMS. WITHOUT TOLERANCE ARE NOT CONTROL DIMS.



MOTAGEAUSSCHNITT
MOUNTING CUT-OUT



250V

16A

BEMESS.SPANNUNG
RATED VOLTAGE

BEMESS.STROM
RATED CURRENT

5	SCREW	STEEL WITH NICKLE PLATING
4	SCREW	STEEL WITH NICKLE PLATING
3	PE CONTACT	BRASS WITH NICKLE PLATING
2	COVER	PC
1	CONTACT CARRIER	PC
ROHSTOFF-NR. R.PART NO.	TYP PART NAME	WERKSTOFF MATERIAL

MAX. NRN./NOS. ?		MODIFICATION		CAT.NO.: 1873880000	
SCALE: 2/1 SUPERSEDES: SUPERSEDED BY:	DRAWN	DATE	NAME	Weidmüller HDC HA 16 FC Buchseneinsatz Female Insert	
	RESPONSIBLE	24.10.2005	LIU_F		
	CHECKED	31.10.2005	Zhang_T		
APPROVED		PRODUCT FILE:		DRAWING NO. ISSUE NO.	