

Powerful Circuit Protection

UL 489 and UL 1077 – AC/DC Rated Miniature Circuit Breakers

Circuit Protection

Engineered Protection for Automation and Process Applications

- Thermal magnetic
- Available for B, C or D curve characteristics
- Common amperage values available 1A to 63A (see back page)

Design Flexibility

- 1-, 2- and 3-pole options
- Optional accessory modules for signalling, change-over and remote tripping
- Optional cuttable busbars and busbar accessories

Robust and Reliable

Wide operating temperature from -35°C...+70°C



Easy Accessory Connection

Snap-together construction
(No screws or extra parts needed)

Global Approvals

UL, CSA, IEC, CE



Pharmaceutical and Food



Chemical, Oil and Gas



Automotive Manufacturing



Rail Vehicles



