






The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Weidmueller exclusively reserves the right to file for patents, utility models or designs.

© Weidmueller Interface GmbH & Co. KG

The English version is binding



210	585	326	341	629	PV SUN COVER 30/19/18	8000087025
210	395	291	341	439	PV SUN COVER 37/30/18	8000087024
220	225	291	351	269	PV SUN COVER 56/30/21	8000086576
Mass Dim. E	Mass Dim. D	Mass Dim. C	Mass Dim. B	Mass Dim. A	Typ Part name	Bestell-Nr. Cat.no.

General Tolerances: ☐ WN700144-W.. ☐ WN 212010 ☒ ISO 2768-mK			Tolerances ISO 8015		
Changes:					
Part No. 1446131			Weidmüller 		
Drawings Assembly			76501		
Drawn Blank, Nikolai			Drawing no. 1		
Responsible Schütz, David			Scale: 1/3 Sheet 1 / 3		
Approved Blank, Nikolai			18.05.2022		
			PV SUN COVER ...		
			Sun Cover		
			Sonnenschutz		