



Product Service

CERTIFICATE

No. B 033299 0456 Rev. 00

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergsstr. 16
32758 Detmold
GERMANY

Certification Mark:



Product:

Switching power supply unit (SWITCHING MODE POWER SUPPLY)

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.

Test report no.: 682101902890

Valid until: 2024-06-04

Date, 2019-06-13


(Yager Bi)



Product Service

CERTIFICATE

No. B 033299 0456 Rev. 00

Model(s): PRO ECO 240W 24V 10A
PRO ECO 240W 48V 5A

Brand Name: Weidmüller

Weidmüller

Parameters:

Rated Input : 100-240VAC, 50/60Hz, 3.5 -1.5A or
120-340VDC, 2.5 - 1.0A

Rated Output : 24VDC, 10A (For model PRO ECO 240W 24V 10A),
48VDC, 5A (For model PRO ECO 240W 48V 5A)

Construction : Built-in

Construction : Built
Protection Class : I

Protection Class : I
Degree of Protection : IPX0

Remarks:

- Remarks :**

 - When installing the equipment, all requirements of the mentioned standard must be fulfilled.
 - The output is hazardous power source, when installing the equipment into end system, care must be taken that the output and associated wire(s) should not be touched.
 - It's built-in component, suitable enclosure should be provided in end system.
 - Clearance was evaluated for operating altitude up to 3000m above sea level.
 - Refer to the installation and operating instruction from manufacturer for the details of loading condition and operating temperature.

Tested according to: EN 62368-1:2014/A11:2017

Production Facility(ies): 057937