






WEITERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
Zuwendungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksmustererhaltung vorbehalten.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. ALL RIGHTS RESERVED IN THE EVENT OF THE GRANT OF A PATENT, UTILITY MODEL OR DESIGN.

MASSE OHNE TOLERANZ SIND KEINE PRUEFMASSE
DIMS. WITHOUT TOLERANCE ARE NOT CONTROL DIMS.



MOTAGEAUSSCHNITT
MOUNTING CUT-OUT

500V 16A

BEMESS.SPANNUNG BEMESS.STROM
RATED VOLTAGE RATED CURRENT

5	SCREW	STEEL WITH NICKLE PLATING
4	SCREW	STEEL WITH NICKLE PLATING
3	PE CONTACT	BRASS WITH NICKLE PLATING
2	COVER	PC
1	CONTACT CARRIER	PC
ROHSTOFF-NR. R.PART NO.	TYP PART NAME	WERKSTOFF MATERIAL

MAX. NRN./NOS. ?

SCALE: 2/1

SUPERSEDES:

SUPERSEDED BY:

MODIFICATION

DRAWN

CHECKED

APPROVED

DATE

24.10.2005

31.10.2005

NAME

LIU_F

Zhang_T

CAT.NO.: 1211600000

Weidmüller

HDC HE 24 FC
Buchseneinsatz
Female Insert

DRAWING NO.

ISSUE NO.

PRODUCT FILE: