




The reproduction, distribution and utilization of this document as well as the communication of its contents without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Weidmueller exclusively reserves the right to file for patents, utility models or designs.

© Weidmueller Interface GmbH & Co. KG

The English version is binding



M 1/1

Allgemeinguetliche Kundenzeichnung, aktueller Stand nur auf Anfrage
 General customer drawing, topical version only if required

Default tolerance ± 0.5

WBC-P-60R-25	2905300000	25mm ²
WBC-P-60R-16	2905280000	16mm ²
WBC-P-60R-10	2905260000	10mm ²
Name	Mat. No.	Wire range

General Tolerances: <input type="checkbox"/> WN700144-W.. <input type="checkbox"/> WN 212010 <input type="checkbox"/> ISO 2768-mK		Tolerances ISO 8015	
Changes:		78153	0 Index
Mat. No. (SAP)			
Drawings Misc		Scale: 3:2	Sheet 1 / 1
Drawn	Li, Angus	WBC-P-60R-.. Battery plug connector Akku stopfen stecker	
Responsible	Li, Angus		
Approved	Xu, Shary		
		23.11.2022	

A4