

接线示意图		接口定义说明	
PNP输入 (2线制)		M12x8 I/O IN/OUT/IO-Link Pin1 +24V 2A Pin2 CH.B:Input/Output 2A Pin3 0V Pin4 CH.A:Input/Output 2A/IO-Link Pin5 n.c.	
PNP输入 (3线制)			
PNP输出			
IO-LINK CLASS A		7/8" POWER Pin1 GND U_L Pin2 GND U_S Pin3 FE(PE) Pin4 +24V U_S Pin5 +24V U_L M12x2 NET Pin1 TD+ Pin2 RD+ Pin3 TD- Pin4 RD- Pin5 BUS	
供电			

