

## Specification Text - Enclosure, Polyester

**75 mm x 80 mm x 55 mm ... 405 mm x 400 mm x 120 mm (Hight x Width x Depth)**

### Specification Text short:

|                       |                                                                |
|-----------------------|----------------------------------------------------------------|
| Manufacturer:         | Weidmüller                                                     |
| Brand:                | Klippon®                                                       |
| Type:                 | Terminal box, junction box, distribution box                   |
| Enclosure range:      | Klippon POK                                                    |
| Material:             | Glass fibre-reinforced polyester                               |
| Lid:                  | 4x captive fixing screws (Cross-Slot), hinge as option         |
| Ambient temperatures: | -40 °C ≤ Tamb ≤ +100 °C (DIN EN 62208), including aging cycles |


### Specification Text long:

|                         |                                                                                                          |
|-------------------------|----------------------------------------------------------------------------------------------------------|
| Manufacturer:           | Weidmüller                                                                                               |
| Brand:                  | Klippon®                                                                                                 |
| Type:                   | Terminal box, junction box, distribution box                                                             |
| Enclosure range:        | Klippon POK                                                                                              |
| Description:            | Klippon POK 082306                                                                                       |
| Article number:         | 1305850000                                                                                               |
| Material:               | Glass fibre-reinforced polyester                                                                         |
| Manufacturing process:  | Hot pressing technique.                                                                                  |
| Wall thickness:         | Enclosure base ≥ 3.5 mm, Draft angle 1 to 2 ° / lid 3.5 mm                                               |
| IP / NEMA Rating:       | IP66 (EN 62208, DIN EN 60529) / NEMA 4, 4X (UL 50E, CSA C22.2)                                           |
| Surface:                | untreated, silver grey                                                                                   |
| Dimensions (H x W x D): | 75 mm x 230 mm x 56 mm                                                                                   |
| Lid:                    | 4x captive fixing screws (Cross-Slot), hinge as option                                                   |
| Sealing for lid:        | Single (non-jointed) chloropren O-ring with compression control, to prevent damage to the sealing gasket |
| Earth bolt:             | Internal: Screw connection / External: As option                                                         |
| Enclosure attachment:   | 4x captive fixing screws (Cross-Slot)                                                                    |
| Ambient temperatures:   | -40 °C ≤ Tamb ≤ +100 °C (DIN EN 62208)                                                                   |
| Impact resistance:      | IK 08 (5J) (DIN EN 50102)                                                                                |

## Specification Text - Enclosure, Polyester

75 mm x 80 mm x 55 mm ... 405 mm x 400 mm x 120 mm (Hight x Width x Depth)

Klippon POK 082306



### Options:

Label fixing sets:

Stainless steel V4A / 316L / 1.4404, screwed or fixed by rivets. Punched silicon gasket with compression control for the label and its silicon gasket, to ensure the IP rating.

Mounting plates:

Galvanized sheet steel

Earth bolt:

Internal / external: M10 of stainless steel V4A / 316L / 1.4404 or M10 of brass or M6 of stainless steel V4A / 316L / 1.4404 or M6 of brass

Wall mounting brackets:

Set with 4 external brackets, stainless steel V2A / 304, 1.4301

Assembly of terminals:

All terminal blocks of type Klippon® Connect. All DIN rails vertical mounting, horizontal mounting as option. Terminal marker horizontal. Hazardous areas: All terminals for intrinsically safe circuits are colored blue, for non-intrinsically safe circuits are colored dark beige. On request: Assembly with control stations (switches, push buttons, lights, indicators).

**Specification Text - Enclosure, Polyester****75 mm x 80 mm x 55 mm ... 405 mm x 400 mm x 120 mm (Hight x Width x Depth)**

Certifications:                      For assembled resp. empty enclosures  
                                         Lloyd's Register  
                                         cULus  
                                         Russian Maritime Register of Shipping  
                                         OIT Certification, Russia, Non-Containment, industrial applications

**Weidmüller Interface GmbH & Co. KG**

Postfach 3030  
32720 Detmold  
Klingenbergstraße 16  
32758 Detmold  
Phone +49 (0) 5231 14-0  
Fax +49 (0) 5231 14-292083  
E-Mail [info@weidmueller.com](mailto:info@weidmueller.com)  
Internet [www.weidmueller.com](http://www.weidmueller.com)

You can find your local contact  
on the internet at:  
[www.weidmueller.com/countries](http://www.weidmueller.com/countries)