

Product Discontinuation for various terminal blocks and their accessories

Dear Sir or Madam,

the products listed below are intended to be discontinued and will no longer be available after a transitional period. Please pass on this product information to your employees and possibly to your customers. All of these product discontinuations have been made to support our continued commitment for improvement and ongoing product development.

1. Initial situation

Over the past years, the requirements and conditions within the target applications of our products have continuously evolved. This development has led to a decline in demand for specific products, making it increasingly challenging to continue production in an economically sustainable manner.

In light of these developments, we have decided to discontinue the manufacturing of the products listed below and hereby officially announce their phase-out.

Of course, we offer suitable successor products that meet current market demands and provide a future-proof alternative.

2. Schedule / Availability

The articles listed below will be discontinued on 30.04.2027.

3. List of affected articles / follow-up

1010600000	WNT 2.5 10X3 BE	→ no follow-up
1010800000	WNT 6 10X3 BE	→ no follow-up
1010900000	WNT 10 10X3 BE	→ no follow-up
1020700000	WDU 2.5/10 BEZ	→ 1020000000
1021000000	WDU 4/10	→ 1020100000
1021600000	WDK 2.5 K	→ no follow-up
1025700000	WDK 2.5/10	→ 1021500000
1056600000	WQL 2/WDU10-2.5	→ no follow-up
1060090000	WAP WDU2.5N/4N GE	→ no follow-up
1062290000	WTR 2.5 STB2.3 RT	→ 1855620000
1063700000	KISC M6X16-Z3	→ no follow-up
1066000000	WZAD 70/95	→ no follow-up
1072210000	WAP 2.5-10 VI	→ no follow-up
1072300000	WQV 70/95-PEN	→ no follow-up
1072400000	WQV 120-PEN	→ no follow-up
1072660000	WBB WDK2.5/BL5.08	→ no follow-up
1074680000	WAP WTR2.5/ZZ BL	→ no follow-up

1079600000	WQB PEN 16N	→ no follow-up
1167440000	IL WMF2.5 BLZ OR	→ no follow-up
1167630000	FUCR SW	→ no follow-up
1167680000	FUCR 100-250V SW	→ no follow-up
1186630000	WDU 50N IR	→ 1820840000
1247330000	WAH 70 SW	→ 1064560000
1248980000	WAH 185/300 SW	→ no follow-up
1252070000	ZDU 2.5/2X2AN/LD+ WS	→ no follow-up
1278810000	1170-21-15A	→ no follow-up
1287860000	TBS 2	→ no follow-up
1305230000	AH WDT 2.5 BT	→ no follow-up
1305240000	WAP WDT 2.5 BT	→ no follow-up
1305250000	WAP WDT 2.5 AT	→ no follow-up
1305310000	WDT 2.5 BT	→ no follow-up
1305320000	WDT 2.5 AT	→ no follow-up
1312540000	STB 36.8/IH/RT WTL6/1	→ no follow-up
1319040000	WF 5/32	→ no follow-up
1319050000	WF 6/32	→ no follow-up
1319060000	WF 8/32	→ no follow-up
1319070000	WF 10/32	→ no follow-up
1319080000	WF 12/32	→ no follow-up
1324100000	SL 5.08/4/WDK2.5 OR	→ no follow-up
1345280000	WTL 6/1/TNSC/EN	→ 1934810000
1361910000	WTR 4/ZZ GN	→ no follow-up
1393350000	WDU 6 IR	→ 1020200000
1393380000	WDU 10 IR	→ 1020300000
1393390000	WDU 16 IR	→ 1020400000
1393400000	WDU 35 IR	→ 1020500000
1393410000	WDU 35N IR	→ 1040400000
1393420000	WDU 70N/35 IR	→ 9512190000
1393430000	WDU 95N/120N IR	→ 1820550000
1403050000	KLBUE 10-20 RC TS27	→ no follow-up
1403070000	KLBUE 3-8 RC TS27	→ no follow-up
1415510000	WDK 10 L	→ no follow-up
1416880000	WTL 6/5 EN STB RE	→ no follow-up
1422430000	WPE 50N IR	→ 1846040000
1438210000	WP 2.5/1AN/2	→ no follow-up
1530040000	ZEI 6 BL	→ 1791190000
1771830000	KSBR/3 ZTL6	→ no follow-up
1781040000	WQL 3 WF12	→ no follow-up
1781720000	WDU 2.5 PACK	→ 1020000000
1781740000	WDU 6 PACK	→ 1020200000
1791250000	FM 4/TS35	→ 0687900000
1833460000	WDU 16 BR	→ no follow-up
1853970000	AP SAK4-10 GR 7042	→ 0117960000

1857840000	TW 4 SAK4-10 GR 7042	→ no follow-up
1865510000	ZTTR 2.5	→ no follow-up
1871500000	WAP WTL6/1 KGR	→ no follow-up
1878650000	WFF 300/AH O.PS	→ 1029700000
1897010000	QL 2 WTL6/4FF	→ no follow-up
1897030000	QL 4 WTL6/4FF	→ no follow-up
1897090000	QL 10 WTL 6/4 FF	→ no follow-up
1897130000	Q 4 WTL 6/4FF	→ no follow-up
1937670000	ASK 1/EN LD 24V AC/DC DB	→ 2893000000
1967090000	VH 27.4/8/6.4	→ no follow-up
1967100000	VH 36.1/8/6.4	→ no follow-up
1967110000	VH 25.2/8/6.4	→ no follow-up
2036720000	ANSF 1X1/43 RV	→ no follow-up
2038880000	SMSE FA/2.8/2 SAK4S	→ no follow-up
2043570000	STFA 2.8/2 SAK4SS	→ no follow-up
2334730000	ADHB/8 WTL35	→ no follow-up
2436360000	WTR 4/ZZ STB/O.TNHE	→ 1905100000
2436390000	WTR 4 STB/O.TNHE	→ 7910210000
2492370000	WMF 2.5 DI OR	→ no follow-up
2550770000	WQB 7 WTL 6/4 FF	→ no follow-up
2550780000	WQB 10 WTL 6/4 FF	→ no follow-up
2551490000	WQB 6 WTL 6/4 FF	→ no follow-up
2615090000	SQV 6/3	→ no follow-up
2615100000	SQV 6/4	→ no follow-up
2615110000	SQB 3/2	→ no follow-up
2615120000	SQB 3/3	→ no follow-up
2615130000	SQB 3/4	→ no follow-up
2615170000	SQBA 4/3	→ no follow-up
2615180000	SQBA 4/4	→ no follow-up
2615220000	SRQB 4/2	→ no follow-up
2615230000	SRQB 4/3	→ no follow-up
2615240000	SRQB 4/4	→ no follow-up
2615270000	SSI 4	→ no follow-up
2616220000	F/HOLDER ASK1/EN/SMT 24VDC BFI 800K	→ no follow-up
2725290000	WPD 204 2X25/4X16+6X10 2XRD	→ no follow-up
2725300000	WPD 304 3X25/6X16+9X10 3XRD	→ no follow-up
2725330000	WPD 305 3X35/6X25+9X16 3XRD	→ no follow-up
2725420000	WPD 205 2X35/4X25+6X16 2XBK	→ no follow-up
2725430000	WPD 305 3X35/6X25+9X16 3XBK	→ no follow-up
2868500000	WAP WTL 6 GR	→ no follow-up
2868510000	WAP WTL 6 SW	→ no follow-up
2874540000	WPD 330CC 3X50/3X50 BN	→ no follow-up
2874590000	WPD 331CC 3X95/3X95 BN	→ no follow-up

2890860000	STGF PPT/35	→ no follow-up
2932430000	WAP WDU2.5N/4N WS	→ no follow-up
2932440000	WAP WDU2.5N/4N RT	→ no follow-up
3008760000	SK RT SAKS3 Z	→ no follow-up
3008770000	SK SW SAKS3 GZ	→ no follow-up
3011910000	VH 28.1/8/6.4	→ no follow-up
7940099061	ST6 N/ EN W/TEST SOCKET	→ no follow-up
7940099113	ST5P1 V1 / EN	→ no follow-up
7940125627	WSI4/2 C/W 100ohm+ZENER DIODE	→ no follow-up
7940128572	BUCHA ST6 E ST6T - C458535	→ no follow-up
8000011998	MSTL W WF AND WFF OVERVIEW	→ no follow-up
8000017523	MSTL W Z WDU_WDK1.5-R3.5 ZDUA-N	→ no follow-up
8000024865	MSTL W WPD BUILDING INSTALLATION	→ no follow-up
8000028114	MSTL A 2.5-4	→ no follow-up
8000035239	SB A WEICOS ACCESSORIES	→ no follow-up
8000062803	SAKDU series FS and DT	→ no follow-up
8000062804	SAKDU series overview	→ no follow-up
8731670000	WTR 2.5/O.TNHE STB2.3	→ 1855620000
9158340001	KDKS1PE/SMT 10-60VAC/DC BFI H+	→ 1518300000 / 1518330000
9158350001	KDKS1PE/SMT 100-250VAC/DC BFI H-	→ 1518330000
9201630000	WQV PEN 95N/120N	→ no follow-up
9502550000	QL 3 SAKK4	→ 9502540000
9502660000	QL 3 SAKK10	→ 9502650000
9502670000	QL 4 SAKK10	→ 9502650000
9509640000	KDKS 1/EN4 O.TNHE	→ 9503350000
9906800000	KDKS1 W/1 FREE ISSUED COMP.	→ no follow-up
9906840000	KDKS1 W/SBL, W/O LEVER	→ no follow-up
9906900000	KDKS1 W/OUT SBL & LOWER CLAMP	→ no follow-up
9908690001	Lever SMT BFI 100-250VUC H+	→ 1720950000
0105260000	ASK 1/EN/VH OR	→ 0456360000
0114100000	QL 2 SAKB10	→ no follow-up
0117900000	AP SAK4-10 RT	→ 0117960000
0117910000	AP SAK4-10 I	→ no follow-up
0135200000	STB 13.5/D6/4/M4 SAKA10	→ no follow-up
0136300000	BFSC M4X6 MS	→ no follow-up
0138000000	P 14/2 D01 RS SAKS4	→ no follow-up
0164400000	SS M3 D 128-A 3	→ no follow-up
0190260000	TSCH 6 DK1 S4	→ no follow-up
0191600000	QL 4 SAKS1	→ no follow-up
0298900000	BFSC M4X35	→ no follow-up
0309800000	BFSC M3X35	→ no follow-up
0345600000	BFSC M5X45	→ no follow-up
0346100000	SS M5 D 128-A 5	→ no follow-up

0354760000	EK 35	→ no follow-up
0366860000	TSCH 3 SAKD2.5 N	→ no follow-up
0376960000	ASK 1/DM	→ no follow-up
0377200000	KISC M3X15/6 SAK2.5 CU5	→ no follow-up
0379400000	STB 6/D3.7/2.3/M3 SAKR	→ no follow-up
0380380000	AP ASK1 BL	→ 0380360000
0428910000	SK SW SAKS3 GZ	→ no follow-up
0457000005	Q 5 SAK6N	→ no follow-up
0470500000	QL 4 SAK10	→ no follow-up
0471000000	QL 10 SAK16	→ no follow-up
0474580000	ASK 1/EN BL	→ 0474560000
0479720000	MF 1/6 2X6.3/2.8	→ no follow-up
0499560000	SAK 2.5/10/35	→ 0380460000
0526760000	ISPF QB75 RT	→ 0526700000
0526780000	ISPF QB75 BL	→ 0526700000
0556660000	SH 3	→ no follow-up
0565100000	QL 4 SAK35N	→ no follow-up
7940102239	AKZ 4,1 POLE,CH,PA,BG	→ no follow-up
7940102240	AKZ 4,1 POLE,AL,PA,BG	→ no follow-up
2436420000	WTR 4/ZZ/O.TNHE	→ 1905090000

For further questions or if you need any additional assistance or information, please contact your local sales office directly.
All contacts for sales representatives are available here: <http://www.weidmueller.com/contact>

Best regards

Product Management Modular Terminal Blocks
Business Unit Rail Mounted Components

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26, 32758 Detmold, Germany

Weidmüller – Your partner in Industrial Connectivity
We look forward to sharing ideas with you – **Let's connect.**