

Workplace Solutions

swifty[®] CS: The Smart Cable Cut & Strip Tool

Cut it. Strip it. Fix it.

Looking for a fast and effortless solution for cutting and stripping cables? With the swifty[®] CS (Cut & Strip), you'll always have the perfect tool on hand — whether you are right- or left-handed!

This screwdriver with a combined cutting and stripping attachment combines two functions in one, making electrical installations easier than ever. The swifty[®] CS is ideal for screw and spring clamp terminals, ensuring a fast and efficient workflow.

Stripping: PVC-insulated fine-stranded and solid conductors up to 2.5 mm² (14 AWG)

Cutting: Copper conductors: single-stranded up to 1.5 mm² (16 AWG) and fine-stranded up to 2.5 mm² (14 AWG)

Thanks to its innovative attachment, the swifty[®] CS simply slides onto uninsulated screwdrivers (3.5 mm blade diameter) — so you can start working immediately without switching tools!

Why swifty[®] CS?

- **Minimal effort** — thanks to an ergonomic grip design
- **Versatile** — suitable for right- or left-handed users
- **Automatic opening** — for fast and effortless operation
- **Adjustment wheel** — for precise stripping support
- **One-handed operation** — keeping your other hand free for extra stability
- **Compact & always ready** — fits in any tool bag

swifty® CS: Combined Stripping and Cutting Tool

Versatile and efficient

Buy the swifty® CS attachment individually or go for the complete set — the cutting and stripping attachment combines two functions in one, making electrical installations easier than ever.

Flexible options for every professional

With the swifty® CS, you'll save time, effort, and hassle — always having the right tool within reach. Choose the standalone attachment to upgrade your existing screwdriver (3.5 mm blade diameter), or opt for the complete set for maximum convenience. Its ultra-compact, one-handed design makes it perfect for panel builders, electricians and installers on the go.

The ultimate tool for electrical installations

Ideal for screw and spring clamp terminals, it handles PVC-insulated fine-stranded and solid conductors up to 2.5 mm² (14 AWG) and cuts copper conductors — single-stranded up to 1.5 mm² (16 AWG), fine-stranded up to 2.5 mm² (14 AWG). Whether right- or left-handed — the swifty® CS is suitable for everyone!




swifty® CS tool set



Cut it.



Strip it.



Fix it.

Ordering Data

Type	Description	Order no.
swifty® CS	Cutting tool w/o screwdriver for one-handed operation	9006020000
swifty® CS Set	Cutting & stripping tool with screwdriver	9006060000

Supporting products in Workplace Solutions and accessories



Wire Processing Center

Optimize your panel building workshop processes with perfectly coordinated solutions for every phase of your production chain.



Crimping Tools

Reliable crimping tools that let you connect wire-end ferrules and contacts in a flash.



Screwdrivers

Weidmuller screwdrivers are ergonomic, safe and powerful. A large assortment is available for every field of application in electrical engineering.

Discover the future of workplace solutions!

Contact us today at weidmuller.com/sales to learn more about how our swifty® CS tool set can help you achieve your panel shop goals.



Visit our website



Visit our eShop