

# TEST REPORT

**Report No.:** SET2014-02575

**Product:** Switching Power Supply

**Model No. :** PRO MAX 480W 48V 10A, PRO MAX 480W 24V 20A

**Brand Name:** Weidmüller

**Applicant:** Weidmüller Interface GmbH & Co.,KG

**Issued by:** CCIC Southern Electronic Product Testing (Shenzhen) Co., Ltd.

**Lab Location:** Electronic Testing Building, Shahe Road, Xili, Nanshan District,  
Shenzhen, 518055, P. R. China

**Tel:** 86 755 26627338 **Fax:** 86 755 26627238



This test report consists of **14** pages in total. It may be duplicated completely for legal use with the approval of the applicant. It should not be reproduced except in full, without the written approval of our laboratory. The client should not use it to claim product endorsement by CCIC-SET. The test results in the report only apply to the tested sample. The test report shall be invalid without all the signatures of testing engineers, reviewer and approver. Any objections must be raised to CCIC-SET within 15 days since the date when the report is received. It will not be taken into consideration beyond this limit.

## Test Report

**Product**..... Switching Power Supply  
**Model No.** ..... PRO MAX 480W 48V 10A, PRO MAX 480W 24V 20A  
**Applicant**..... Weidmüller Interface GmbH & Co.,KG  
**Applicant Address**..... Klingenbergstraße 16 32758 Detmold Germany  
**Manufacturer** ..... Weidmüller Interface GmbH & Co.,KG  
**Manufacturer Address** ..... Klingenbergstraße 16 32758 Detmold Germany  
**Test Standards**..... SEMI F47-0706  
 <Specification for semiconductor processing equipment  
 voltage sag immunity>  
**Test Result**..... Pass  
**Tested by** ..... Zhu Qi  
 \_\_\_\_\_  
 Zhu Qi, Mar. 31,2014  
**Reviewed by** ..... Zhang Peng  
 \_\_\_\_\_  
 Zhang Peng, Mar. 31,2014  
**Approved by** ..... Wu Lian  
 \_\_\_\_\_  
 Wu Lian, Mar. 31,2014

