


WEIDMÜLLER INTERFACCE GmbH & Co. KG

WIEDERHOLUNG: VERBODEN. VERWERTUNG DES INHALTS SIND VERBODEN. SOWEIT NICHT AUSDRÜCKLICH GESTATET.
ZUWIDERHANDLUNG: VERFÜHRUNG ZU SCHADENSTÄTZE. ALLE RECHTE DER FÜR DEN PATENT-, GEBRAUCHSMUSTER-, ODER GESCHMACKSMUSTERENTWURF VORBEHALTEN.
THE REPRODUCTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMÜLLER RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS.



Additional product documents				1.						Tolerances: ISO 2768-mK							
				2.													
					Date		Name		Weidmüller								
					Drawn		14/02/2022							wes0212			
					Checked		24/03/2022		wes0212		PV 220S0F4CXXV000TAPA15PWW						
					Criterion for print					Description:							
					1 : 1			A3									
					Customer:												
					WEIDMÜLLER, S.A.												
					Customer-No:												
					104000066												
1	Design Modification		14/06/2022	wes0212						Drawing-No / Material-No:				drw Index			
0			14/02/2022	wes0212						8000093501				1		1/4	
Index	Brief Description		Date	Name						Customer Description:							

drw Index	Sheet
1	1 / 4