



## Product Service

# CERTIFICATE

No. B 033299 0447 Rev. 00

**Holder of Certificate:** Weidmüller Interface GmbH & Co. KG

Klingenberstr. 16  
32758 Detmold  
GERMANY

## Certification Mark:



## Product:

## Power supply

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.

**Test report no.:** 682101900830

Valid until: 2024-03-21

Date. 2019-03-22

(Yager Bi)



Product Service

# C E R T I F I C A T E

No. B 033299 0447 Rev. 00

**Model(s):** PRO INSTA 60W 12V 5A, PRO INSTA 60W 24V 2.5A  
PRO INSTA 30W 5V 6A

**Brand Name:** Weidmüller

**Weidmüller** 

## Parameters:

Rated Input : 100-240VAC, 50-60Hz, 1.5-0.7A; or 120-340VDC, 0.8-0.25A  
(for models: PRO INSTA 60W 12V 5A, PRO INSTA 60W 24V 2.5A);  
100-240Vac, 50-60Hz, 1.0-0.5A; or 120-340Vdc, 0.5-0.2A  
(for model: PRO INSTA 30W 5V 6A)

Rated Output : 12VDC/5A (for model: PRO INSTA 60W 12V 5A)  
24VDC/2.5A (for model: PRO INSTA 60W 24V 2.5A)  
5VDC/6A (for model: PRO INSTA 30W 5V 6A)

Protection Class : II

Degree of Protection : IPX0

## Remarks :

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Maximum operating temperature is 70°C.
- This power supply contains output with hazardous power source, when installing into end system, care must be taken that the output and associated wire(s) may not be touched.
- Built-in type equipment, suitable enclosure and type of supply connection should be provided by end system.

**Tested according to:** EN 62368-1:2014/A11:2017

**Production Facility(ies):** 069022