


[illegible]

8 7 6 5 4 3 2 1

F

E

D

C

B

A

8 7 6 5 4 3 2 1

BOTTOM SIDE

LEFT SIDE

FRONT SIDE

RIGHT SIDE

BACK SIDE

300

315

542

747

655

790

430

565

Ø9

Additional Product Documents

-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

1.	-	
2.	-	
	Date	Name
Drawn	03.06.2021	wes0212
Checked		
Criterion for print		
1:8	A3	
Customer:		
WEIDMÜLLER, S.A.		
Customer-No:		
104000066		

Tolerances: ISO 2768-mK

Description:

PV 216S0F4CXXV0O0TXPX15LWW


Drawing-No / Material-No:	drw Index	Sheet
8000078885	0	1 / 15

Customer Description: -


WEITERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
Zu widerhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksmusterrechte vorbehalten.
THE REPRODUCTION, DISTRIBUTION AND UTILISATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMÜLLER EXCLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS

WEIDMÜLLER INTERFACE GmbH & Co. KG


BOTTOM SIDE



FRONT SIDE




SECTION VIEW



SECTION A-A

BACK SIDE



Additional Product Documents				1. -			Tolerances: ISO 2768-mK				
				2. -							
				Date		Name		Weidmüller			
				Drawn		03.06.2021 wes0212					
				Checked							
				Criterion for print							
				1:8		A3		PV 216S0F4CXXV0O0TXPX15LWW			
				Customer:							
				WEIDMÜLLER, S.A.							
				Customer-No:							
				104000066				Drawing-No / Material-No:		drw Index	Sheet
								8000078885		0	2 / 15
								Customer Description: -			
Index	Brief Description			Date	Name						