



Product Service

CERTIFICATE

No. B 033299 0506 Rev. 01

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product:

**Switching power supply unit
(DC Uninterrupted Power Supply)**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6821020022203

Valid until: 2026-01-06

Date, 2025-05-09

(Yager Bi)

CERTIFICATE

No. B 033299 0506 Rev. 01

Model(s): CP DC UPS 24V 40A

Brand Name: Weidmüller

Weidmüller 

Parameters:

Rated Input: 24VDC, 52A MAX
Input Voltage Range: 20-30VDC
Rated Output: 24VDC, 40A
Degree of Protection: IPX0

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- The maximum operating temperature is 70°C. Refer to the installation and operating instruction from manufacturer for the details of loading condition and operating temperature.
- Functional insulation is provided between input circuit and output circuit, and between input circuit and enclosure.
- This built-in equipment should be connected to a source which is insulated from the mains supply by double or reinforced insulation.
- Built-in type equipment, suitable enclosure should be provided by end system.
- When installed the unit, there must be at least 5 cm distance from bottom for ventilation.

Tested according to: EN 62368-1:2014/A11:2017