



 WEIDMÜLLER INTERFACE GmbH & Co. KG



36	59,50	2,343
34	56,00	2,205
32	52,50	2,067
30	49,00	1,929
28	45,50	1,791
26	42,00	1,654
24	38,50	1,516
22	35,00	1,378
20	31,50	1,240
18	28,00	1,102
16	24,50	0,965
14	21,00	0,827
12	17,50	0,689
10	14,00	0,551
8	10,50	0,413
6	7,00	0,276
4	3,50	0,138
n	L1 [mm]	L1 [inch]

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

 DIN ISO 2768					CAT.NO.: .	
	80058/3	19.01.15	HELIS_MA	01	C 32283 26	
	MODIFICATION				DRAWING NO. SHEET 01 ISSUE NO. OF 03 SHEETS	
		DATE	NAME	S2L-SMT 3.50/.../90... STIFTLISTE MALE HEADER		
	DRAWN	19.03.2007	LANG_T			
	RESPONSIBLE		AMANN_A			
	CHECKED	21.01.2015	HERTEL_S			
	APPROVED		LANG_T			
SCALE: 2/1				PRODUCT FILE: S2L-SMT 3.50 7272		
SUPERSEDES: .						