



Product Service

CERTIFICATE

No. B 033299 0583 Rev. 01

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product: Power supply

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6821019007903

Valid until: 2030-12-25

Date, 2025-12-29

(Yager Bi)

CERTIFICATE

No. B 033299 0583 Rev. 01

Model(s): PRO INSTA 30W 12V 2.6A,
PRO INSTA 30W 24V 1.3A

Brand Name: Weidmüller

Weidmüller 

Parameters:

Rated Input: 100-240VAC, 50-60Hz, 1.0-0.5A or 120-340VDC, 0.5-0.2A

Rated Output: 12VDC, 2.6A (for model: PRO INSTA 30W 12V 2.6A),

24VDC, 1.3A (for model: PRO INSTA 30W 24V 1.3A)

Protection Class: II

Degree of Protection: IP20

Remark:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Built-in type component, suitable enclosure should be provided by end system.
- Maximum operating temperature is 70°C.
- Clearance was evaluated for operating altitude up to 2000m above sea level.

Tested according to: EN IEC 62368-1:2024/A11:2024