



Product Service

CERTIFICATE

No. B 033299 0584 Rev. 01

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product: Power supply

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6821019008303

Valid until: 2030-12-25

Date, 2025-12-29

(Yager Bi)

CERTIFICATE

No. B 033299 0584 Rev. 01

Model(s): PRO INSTA 60W 12V 5A,
PRO INSTA 60W 24V 2.5A,
PRO INSTA 30W 5V 6A

Brand Name: Weidmüller

Weidmüller 

Parameters:

Ratings:

For model PRO INSTA 60W 12V 5A:

Input: 100-240VAC, 50-60Hz, 1.5-0.7A or 120-340VDC, 0.8-0.25A

Output: 12VDC, 5A

For model PRO INSTA 60W 24V 2.5A:

Input: 100-240VAC, 50-60Hz, 1.5-0.7A or 120-340VDC, 0.8-0.25A

Output: 24VDC, 2.5A

For model PRO INSTA 30W 5V 6A:

Input: 100-240VAC, 50-60Hz, 1.0-0.5A or 120-340VDC, 0.5-0.2A

Output: 5VDC, 6A

Protection Class: II

Degree of Protection: IP20

Remark:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Built-in type component, suitable enclosure should be provided by end system.
- Maximum operating temperature is 70°C.
- Clearance was evaluated for operating altitude up to 2000m above sea level.

Tested according to: EN IEC 62368-1:2024/A11:2024