

IE-PM-RJ45-TH 1963580000/ IE-PS-RJ45-TH-BK 1963590000


Montagehinweis / Mounting information / Références de montage /
Indicaciones de montaje / Informazioni per il montaggio

Weidmüller 

1




video



2




max. Ø7,3


3

Anschluss / Connection			Anwendung / Application				
RJ45 PIN Nr./No.	Farbcode Colour code T568		Profinet	10BT/ 100BT	Gigabit Ethernet	Token Ring ISDN/So	TP-PMD/ ATM
	A	B					
1	WH-GN	WH-OG	YE	•	•		•
2	GN	OG	OG	•	•		•
3	WH-OG	WH-GN	WH	•	•	•	
4	BU	BU	-		•	•	
5	WH-BU	WH-BU	-		•	•	
6	OG	GN	BU	•	•	•	
7	WH-BN	WH-BN	-		•		•
8	BN	BN	-		•		•

4




min. 40 mm
min. 1,6 in.



5



min. 40 mm
min. 1,6 in.



6




**Weidmüller Interface
GmbH & Co. KG**

Postfach 3030
32720 Detmold / Germany

Tel.: +49 (0)5231/14-0
Fax: +49 (0)5231/14-2083
e-mail: info@weidmueller.com
www.weidmueller.com

Montageanleitung siehe
Mounting instructions see
Instructions de montage
Instrucciones de montaje
Istruzioni per il montaggio www.weidmueller.com



**Weidmüller Interface
GmbH & Co. KG**

Postfach 3030
32720 Detmold / Germany

Tel.: +49 (0)5231/14-0
Fax: +49 (0)5231/14-2083
e-mail: info@weidmueller.com
www.weidmueller.com

Montageanleitung siehe
Mounting instructions see
Instructions de montage
Instrucciones de montaje
Istruzioni per il montaggio www.weidmueller.com