Material No.	Artikelname / Article Name	Spezifikation/ Specification	Drehmoment / Torque
9535760000	FPC 30/40/13 TRSP	Deckelschraube / Lid Screw	0,8-1,0 Nm
2860620000	VG M16 - K68/15 5-10	Hutmutter / Cap Nut	2-3 Nm











Technical details:

Up to 4 MPPT (Maximum Power Point Tracking)
2x DC Input per MPPT
1x DC Output per MPPT

Connection type:
Plug-WMC4

Surge voltage arrester
PV system voltage max.: 1100V DC
Requirements class: Type I+II
With remote switch disconnector (breaking & switching capacity acc. to IEC 60947-3 and DC-PV-1)

Rated DC voltage (Un): 1100 V
Rated DC current per input (Inc): 35 A
Rated short-time withstand current per input: 1.25 x Inc
Rated total DC current per MPPT (I out max.): 35 A
Operation ambient temperature: -20°C to +50°C
Degree of Protection: IP65, no direct sunlight

mounting feet enclosed

Additional
Product Documents

Index	Brief Description	Date	Name
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

1. -
2. -

Tolerances: ISO 2768-mK

	Date	Name
Drawn	13.06.2023	wm00038
Checked	17.07.2023	W007064

Criterion for print: 1:5 A3

Customer:

Customer-No:

Weidmüller

Description:
PVC DC 2I 1O 4MPP RD SPD1R WM4 11

Drawing-No / Material-No: 8000115470
drw Index: 0
Sheet: 1 / 1

Customer Description: -

WEITERGABE SOWIE VERVIELFAELTIGUNG DIESES DOKUMENTS, VERWERTUNG UND MITTEILUNG SEINES INHALTS SIND VERBOTEN, SOWEIT NICHT AUSDRUECKLICH GESTATTET.
ZUWIDERHANDLUNGEN VERPFLICHTEN ZU SCHADENERSATZ. ALLE RECHTE FUER DEN FALL DER PATENT-, GEBRAUCHSMUSTER- ODER GESCHMACKSMUSTEREINTRAGUNG VORBEHALTEN.
THE REPRODUCTION, DISTRIBUTION AND UTILISATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICID AUTHORIZATION IS PROHIBITED.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMUELLER EXLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS. UTILITY MODELS OR DESIGNS
WEIDMUELLER INTERFACE GmbH & Co. KG