

Klippon® Relay

CUBESERIES Industrial Relay Modules

With PUSH IN and screw connection options for quick installation

CUBESERIES relay modules, due to their durability and robust design, can reliably switch small loads, decouple systems and multiply signals.

Relay contact versions from 15.6 mm width:

- 1 changeover contact (16 A)
- 2 changeover contacts (8 A)

Relay contact versions from 27 mm width:

- 2 changeover contacts (12 A)
- 4 changeover contacts (7 A)

The relay sockets with PUSH IN and screw technology in various cross-connections enable simple wiring — optimized for use in industrial automation.



Approvals



Discover more at www.weidmuller.com/cubeseries

Features

- New relays with improved amp ratings
 - Allows for a more diversified use case per part
- Multiple cross-connections
 - Less wiring and quicker installation
- Lockable test keys for simple and safe testing
- Relay modules from 15.6 mm width
- Fast wiring with PUSH IN technology
- Multitude of LED & test button configurations to meet any need

CUBESERIES Relays for Universal Use in a Wide Range of Industrial Applications

CRI CUBESERIES Relays

- Voltages: 12, 24, 48 & 110 V DC
- Voltages: 24, 115 & 230 V AC
- Available with or without a test button



Relays – CRI 1 Changeover

Type	Rated control voltage	Test button	Cont. current	Qty	Order no.
CRI10024	24 V DC	No	16 A	10	3052290000
CRI10615	115 V AC	No	16 A	10	3052330000
CRI10730	230 V AC	No	16 A	10	3052340000
CRI10024T	24 V DC	Yes	16 A	10	3052360000
CRI10615T	115 V AC	Yes	16 A	10	3052400000
CRI10730T	230 V AC	Yes	16 A	10	3052410000

Note: More products can be found in the eShop at eshop.weidmuller.com

Relays – CRI 2 Changeover

Type	Rated control voltage	Test button	Cont. current	Qty	Order no.
CRI20024	24 V DC	No	8 A	10	3052430000
CRI20615	115 V AC	No	8 A	10	3052470000
CRI20730	230 V AC	No	8 A	10	3052490000
CRI20024T	24 V DC	Yes	8 A	10	3052510000
CRI20615T	115 V AC	Yes	8 A	10	3052550000
CRI20730T	230 V AC	Yes	8 A	10	3052560000

Note: More products can be found in the eShop at eshop.weidmuller.com

Socket for CRI Relays

Type	Connection	Max. conductor connection ferrule w/ plastic collar	Continuous current: max.	Qty	Order no.
CSI P 2CO	PUSH IN	1.0 mm ²	1CO Relays: 12 A* 2CO Relays: 8 A	20	3052570000
CSI S 2CO	Screw connection	2.5 mm ²	1CO Relays: 12 A* 2CO Relays: 8 A	10	3052590000

Note: * For continuous currents > 12 A up to a max. of 16 A; connections 11 & 21, 12 & 22, 14 & 24 must be bridged with cross-sections at the conductor connections. (This exception does not apply to the UL and CSA approvals.)

CRM CUBESERIES Relays

- Voltages: 12, 24, 48 & 110 V DC
- Voltages: 24, 115 & 230 V AC
- Available with or without a test button & LED



Relays – CRM 2 Changeover

Type	Rated control voltage	Test button	LED Status	Diode	Cont. current	Qty	Order no.
CRM20024	24 V DC	No	No	No	12 A	10	3052730000
CRM20615	115 V AC	No	No	No	12 A	10	3052770000
CRM20730	230 V AC	No	No	No	12 A	10	3052780000
CRM20024T	24 V DC	Yes	No	No	12 A	10	3052800000
CRM20615T	115 V AC	Yes	No	No	12 A	10	3052840000
CRM20730T	230 V AC	Yes	No	No	12 A	10	3052850000
CRM20024TLD	24 V DC	Yes	Yes	Yes	12 A	10	3052870000
CRM20615TL	115 V AC	Yes	Yes	No	12 A	10	3052910000
CRM20730TL	230 V AC	Yes	Yes	No	12 A	10	3052920000

Note: More products can be found in the eShop at eshop.weidmuller.com

Relays – CRM 4 Changeover

Type	Rated control voltage	Test button	LED Status	Diode	Cont. current	Qty	Order no.
CRM40024	24 V DC	No	No	No	7 A	10	3052940000
CRM40615	115 V AC	No	No	No	7 A	10	3052980000
CRM40730	230 V AC	No	No	No	7 A	10	3052990000
CRM40024T	24 V DC	Yes	No	No	7 A	10	3053010000
CRM40615T	115 V AC	Yes	No	No	7 A	10	3053050000
CRM40730T	230 V AC	Yes	No	No	7 A	10	3053060000
CRM40024TLD	24 V DC	Yes	Yes	Yes	7 A	10	3053080000
CRM40615TL	115 V AC	Yes	Yes	No	7 A	10	3053120000
CRM40730TL	230 V AC	Yes	Yes	No	7 A	10	3053130000

Note: More products can be found in the eShop at eshop.weidmuller.com

Socket for CRM Relays

Type	Connection	Max. conductor connection ferrule w/ plastic collar	Continuous current: max.	Qty	Order no.
CSM P 4CO	PUSH IN	1.0 mm ²	2CO Relays: 12 A 4CO Relays: 7 A	10	3053140000
CSM S 4CO	Screw connection	2.5 mm ²	2CO Relays: 12 A 4CO Relays: 6 A	10	3053160000

Discover more about Weidmuller's CUBESERIES relays!

Contact your local Weidmuller sales representative today at www.weidmuller.com/sales.



eshop.weidmuller.com

Weidmuller, Inc
821 Southlake Blvd.
Richmond, Virginia 23236
Telephone: (800) 849-9343
Website: www.weidmuller.com
Email: customerservice@weidmuller.com