

Klippon® Relay

CUBESERIES KITs – Pre-assembled relay modules

Pre-assembled relay modules save time and reduce material numbers

Companies use the pre-assembled CUBESERIES KIT relay modules in industry, mechanical engineering, process engineering and energy systems. The relay modules switch small industrial loads, decouple system parts and efficiently multiply signals. The industrial relays from Europe deliver robustness, reliability and durability.

Pre-assembled, they reduce installation time and material numbers. The CUBESERIES simplifies handling, offers an industrial-grade design and is wired efficiently, quickly and safely via PUSH IN connections and cross-connections.



Your special advantages:

- KIT consisting of relay, socket, retaining clip and status indicator
- 100 % function-tested
- Diverse cross-connections
- Fast wiring with PUSH IN
- Retaining clip with marker holder
- Relay modules from 15.6 mm width with 1 changeover contact (16 A) and 2 changeover contacts (8 A)
- Relay modules from 27 mm width with 2 changeover contacts (12 A) and 4 changeover contacts (7 A)

PUSH IN 





CRI KITS Relay modules

Type	Rated control voltage	Test button	Status-LED	Free-wheeling diode	Connection	Contact type	Continuous current	Qty	Order No.
CRIKIT P 24VDC 1CO L/D	24 V DC		●	●	PUSH IN	1 CO	16 A*	10	3137560000
CRIKIT P 24VDC 1CO L/D/PB	24 V DC	●	●	●	PUSH IN	1 CO	16 A*	10	3137570000
CRIKIT P 24VAC 1CO L	24 V AC		●	●	PUSH IN	1 CO	16 A*	10	3137340000
CRIKIT P 24VAC 1CO L/PB	24 V AC	●	●	●	PUSH IN	1 CO	16 A*	10	3137350000
CRIKIT P 230VAC 1CO L	230 V AC		●	●	PUSH IN	1 CO	16 A*	10	3137360000
CRIKIT P 230VAC 1CO L/PB	230 V AC	●	●	●	PUSH IN	1 CO	16 A*	10	3137370000
CRIKIT P 24VDC 2CO L/D	24 V DC		●	●	PUSH IN	2 CO	8 A	10	3137380000
CRIKIT P 24VDC 2CO L/D/PB	24 V DC	●	●	●	PUSH IN	2 CO	8 A	10	3137390000
CRIKIT P 24VAC 2CO L	24 V AC		●	●	PUSH IN	2 CO	8 A	10	3137400000
CRIKIT P 24VAC 2CO L/PB	24 V AC	●	●	●	PUSH IN	2 CO	8 A	10	3137410000
CRIKIT P 230VAC 2CO L	230 V AC		●	●	PUSH IN	2 CO	8 A	10	3137420000
CRIKIT P 230VAC 2CO L/PB	230 V AC	●	●	●	PUSH IN	2 CO	8 A	10	3137430000
CRIKIT S 24VDC 1CO L/D	24 V DC		●	●	Screw	1 CO	16 A*	10	3137440000
CRIKIT S 24VDC 1CO L/D/PB	24 V DC	●	●	●	Screw	1 CO	16 A*	10	3137450000
CRIKIT S 24VAC 1CO L	24 V AC		●	●	Screw	1 CO	16 A*	10	3137460000
CRIKIT S 24VAC 1CO L/PB	24 V AC	●	●	●	Screw	1 CO	16 A*	10	3137470000
CRIKIT S 230VAC 1CO L	230 V AC		●	●	Screw	1 CO	16 A*	10	3137480000
CRIKIT S 230VAC 1CO L/PB	230 V AC	●	●	●	Screw	1 CO	16 A*	10	3137490000
CRIKIT S 24VDC 2CO L/D	24 V DC		●	●	Screw	2 CO	8 A	10	3137500000
CRIKIT S 24VDC 2CO L/D/PB	24 V DC	●	●	●	Screw	2 CO	8 A	10	3137510000
CRIKIT S 24VAC 2CO L	24 V AC		●	●	Screw	2 CO	8 A	10	3137520000
CRIKIT S 24VAC 2CO L/PB	24 V AC	●	●	●	Screw	2 CO	8 A	10	3137530000
CRIKIT S 230VAC 2CO L	230 V AC		●	●	Screw	2 CO	8 A	10	3137540000
CRIKIT S 230VAC 2CO L/PB	230 V AC	●	●	●	Screw	2 CO	8 A	10	3137550000

*For continuous currents > 12 A up to a maximum of 16 A for the 1 CO versions, the connections 11 and 21, 12 and 22, 14 and 24 must be bridged with suitable cross-sections. When using the PUSH IN socket, this can also be set up with the cross-connections 'CXX JMP 2P xx'.



CRM KITS Relay modules

Type	Rated control voltage	Test button	Status-LED	Free-wheeling diode	Connection	Contact type	Continuous current	Qty	Order No.
CRMKIT P 24V DC 2CO L/D	24 V DC		●	●	PUSH IN	2 CO	12 A	5	3137100000
CRMKIT P 24V DC 2CO L/D/PB	24 V DC	●	●	●	PUSH IN	2 CO	12 A	5	3137110000
CRMKIT P 24V AC 2CO L	24 V AC		●	●	PUSH IN	2 CO	12 A	5	3137120000
CRMKIT P 24V AC 2CO L/PB	24 V AC	●	●	●	PUSH IN	2 CO	12 A	5	3137130000
CRMKIT P 230V AC 2CO L	230 V AC		●	●	PUSH IN	2 CO	12 A	5	3137140000
CRMKIT P 230V AC 2CO L/PB	230 V AC	●	●	●	PUSH IN	2 CO	12 A	5	3137150000
CRMKIT P 24V DC 4CO L/D	24 V DC		●	●	PUSH IN	4 CO	7 A	5	3137160000
CRMKIT P 24V DC 4CO L/D/PB	24 V DC	●	●	●	PUSH IN	4 CO	7 A	5	3137170000
CRMKIT P 24V AC 4CO L	24 V AC		●	●	PUSH IN	4 CO	7 A	5	3137180000
CRMKIT P 24V AC 4CO L/PB	24 V AC	●	●	●	PUSH IN	4 CO	7 A	5	3137190000
CRMKIT P 230V AC 4CO L	230 V AC		●	●	PUSH IN	4 CO	7 A	5	3137200000
CRMKIT P 230V AC 4CO L/PB	230 V AC	●	●	●	PUSH IN	4 CO	7 A	5	3137210000
CRMKIT S 24V DC 2CO L/D	24 V DC		●	●	Screw	2 CO	12 A	5	3137220000
CRMKIT S 24V DC 2CO L/D/PB	24 V DC	●	●	●	Screw	2 CO	12 A	5	3137230000
CRMKIT S 24V AC 2CO L	24 V AC		●	●	Screw	2 CO	12 A	5	3137240000
CRMKIT S 24V AC 2CO L/PB	24 V AC	●	●	●	Screw	2 CO	12 A	5	3137250000
CRMKIT S 230V AC 2CO L	230 V AC		●	●	Screw	2 CO	12 A	5	3137260000
CRMKIT S 230V AC 2CO L/PB	230 V AC	●	●	●	Screw	2 CO	12 A	5	3137270000
CRMKIT S 24V DC 4CO L/D	24 V DC		●	●	Screw	4 CO	6 A	5	3137280000
CRMKIT S 24V DC 4CO L/D/PB	24 V DC	●	●	●	Screw	4 CO	6 A	5	3137290000
CRMKIT S 24V AC 4CO L	24 V AC		●	●	Screw	4 CO	6 A	5	3137300000
CRMKIT S 24V AC 4CO L/PB	24 V AC	●	●	●	Screw	4 CO	6 A	5	3137310000
CRMKIT S 230V AC 4CO L	230 V AC		●	●	Screw	4 CO	6 A	5	3137320000
CRMKIT S 230V AC 4CO L/PB	230 V AC	●	●	●	Screw	4 CO	6 A	5	3137330000



Visit our website for more information
www.weidmueller.com/cubeseries



Visit our online catalogue
for more information