


Klippon® Relay

TERMSERIES-compact - universal relay

Relay modules with maximum vibration resistance

TERMSERIES-compact relay modules with two outputs

The new, ultra-compact complete modules round out the TERMSERIES family. Their relays are integral, which makes them particularly vibration-proof. Thanks to their reliability, even in environments with strong vibrations, they make machines and systems available without restriction. Due to the slim and, above all, flat design, they can be installed anywhere. And since they have the same contours as TERMSERIES, all the accessories in the series can be used - for example for cross-connections.



Your special advantages:

- Extremely compact with a width of only 12.8 mm and a depth of 63 mm
- Integrated status LED for easy function testing
- Compatible with the complete range of TERMSERIES accessories
- Their relays are permanently installed, which makes them particularly vibration-proof
- As a 2 Change Over version




Optimised for fast wiring

The PUSH IN connection technology reduces the wiring time by 75% compared to conventional connection technologies. If the terminal point needs to be released again, all you need to do is apply brief pressure with a conventional screwdriver.

Universally applicable

Can be used in a wide range of applications thanks to different versions and a variety of input voltages. Multi-voltage input of the TERMSERIES with 24-230 V UC and 12-60 V UC available for the first time in an extremely compact design.



100 % function-tested

The function test carried out at our factory, including a check of the dielectric strength of the inputs and outputs, increases safety and also saves time during installation.

Particularly maintenance-friendly

The integrated test tap on each level allows fast, uncomplicated testing with standard test plugs. This simplifies maintenance and troubleshooting during operation.

Technical data

Type	Control side	Contact type / Version	Load side	Clamping range min./max.	Qty	Order No.
TRPL 5VDC 2CO	5 V DC	2 CO contact	250 V AC / 6 A	0,14 - 2,5 mm ²	10	2774050000
TRPL 24VUC 2CO	24 V UC	2 CO contact	250 V AC / 6 A	0,14 - 2,5 mm ²	10	2773990000
TRPL 24VDC 2CO	24 V DC	2 CO contact	250 V AC / 6 A	0,14 - 2,5 mm ²	10	2773960000
TRPL 24-230VUC 2CO	24-230 V UC	2 CO contact	250 V AC / 6 A	0,14 - 2,5 mm ²	10	2773880000
TRPL 230VAC 2CO	230 V AC	2 CO contact	250 V AC / 6 A	0,14 - 2,5 mm ²	10	2773850000
TRPL 120VAC 2CO	120 V AC	2 CO contact	250 V AC / 6 A	0,14 - 2,5 mm ²	10	2773820000
TRPL 12-60VUC 2CO	12-60 V UC	2 CO contact	250 V AC / 6 A	0,14 - 2,5 mm ²	10	2773790000



Visit our website for more information
www.weidmueller.com/termcompact



Visit our online catalogue for more information