



WEITERGABE SOWIE Vervielfaeltigung dieses Dokuments, Verwertung und MitteiluNG seines Inhalts sind verboten, soweit nicht Ausdruecklich gestattet.
ZuWiderhandlungen Verpflichten zu Schadenersatz. Alle Rechte fuer den Fall der Patent-, GebrauchsMuster- oder GeschMacksmustereintragung Vorbehalten.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMUELLER EXCLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS.

© WEIDMUELLER INTERFACE GmbH & Co.KG

MASSE OHNE TOLERANZ SIND KEINE PRUEFMASSE
DIMS. WITHOUT TOLERANCE ARE NOT CONTROL DIMS.

DIE DEUTSCHE VERSION IST VERBINDLICH
THE GERMAN VERSION IS BINDING



P = PITCH
n = NO OF POLES
SHOWN: S2L-SMT 3.50/04/90G

STIFTLAENGE/ PIN LENGTH L	TOLERANZ/ TOLERANCES	36	59,50	2,343
1.5	0	34	56,00	2,205
	-0.3	32	52,50	2,067
1.8	0	30	49,00	1,929
	-0.3	28	45,50	1,791
2.3	0	26	42,00	1,654
	-0.3	24	38,50	1,516
3.2	0	22	35,00	1,378
	-0.3	20	31,50	1,240
3.5	0	18	28,00	1,102
	-0.3	16	24,50	0,965
	0	14	21,00	0,827
	-0.3	12	17,50	0,689
	0	10	14,00	0,551
	-0.3	8	10,50	0,413
	0	6	7,00	0,276
	-0.3	4	3,50	0,138
		n	L1 [mm]	L1 [inch]

For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

DIN ISO 2768

80058/3
19.01.15 HELIS_MA

01

MODIFICATION

DRAWN

19.03.2007

LANG_T

RESPONSIBLE

21.01.2015

AMANN_A

CHECKED

21.01.2015

HERTEL_S

APPROVED

LANG_T

CAT.NO.: .

Weidmüller

C 32283 **26**

DRAWING NO. SHEET 02 OF 03 SHEETS

ISSUE NO.

S2L-SMT 3.50/./90...

STIFTELEISTE
MALE HEADER

PRODUCT FILE: S2L-SMT 3.50

7272