


**WORKPLACE
SOLUTIONS**

Weidmüller 



Workplace Solutions

The new PrintJet MINI


The compact industrial printer for flexible and professional control cabinet labeling

As a cabinet manufacturer, system planner, or technician, you know how crucial precise and durable labeling is for optimizing processes and ensuring clarity within control cabinet infrastructure. With the PrintJet MINI – the compact industrial printer from Weidmüller – you're choosing a smart solution that boosts your efficiency and is perfectly tailored to your needs.

The PrintJet MINI is small, lightweight, and optionally available with a practical transport case. This mobility makes it the ideal choice for on-site service operations or changing work environments. Due to its well-thought-out design, it's easy to transport and can be used flexibly – wherever reliable control cabinet labeling is required.



More information on our Website:
www.weidmueller.com/PJMINI



Orange Transparency – Technology Made Visible

The transparent orange flap of the PrintJet MINI offers full visibility of the printing process – UV-curing ink ensures wipe- and scratch-resistant markings.



Touch & Control – Everything at a Glance, Everything Under Control

The integrated 5" color touch display provides all key information at a glance – from ink levels to printer status. Clear, intuitive, and user-friendly.



Slide & Go – Easy Loading

The automatic slide-out system makes inserting MultiCard markers easier than ever. User-friendly, ergonomic, and efficient – for a smooth workflow with style.



Volume Match – Efficient for Every Printing Need

Whether full or half MultiCards, individual segments, or markers: the PrintJet MINI adapts flexibly – delivering maximum versatility with minimal effort.



Design Meets Function – Quick and Easy Replacement

The included cartridge is easy to clean and can be fully replaced – including the printhead – whenever needed. For maximum user convenience.



Move MINI – Design That Moves With You


Compact, lightweight, and ready for action: with its matching transport case (optional), the PrintJet MINI becomes a mobile all-rounder – wherever precise labeling is needed.

Design meets function – The Benefits of the PrintJet MINI at a Glance

With the PrintJet MINI, we've developed more than just an industrial printer – we've created a mobile solution that combines design, functionality, and efficiency in a compact format.

Thoughtfully designed down to the last detail, it enables precise marking wherever it's needed – flexible, reliable, and intuitive.

The PrintJet MINI stands for modern industrial design that not only optimizes processes, but also sets new standards in mobility and user convenience.

- 
- A man and a woman, both wearing dark blue polo shirts with a logo, are smiling and holding a compact, black and orange industrial printer (PrintJet MINI) in a large, brightly lit industrial facility. The printer has a transparent orange flap and a small screen. The background shows a long, modern factory aisle with overhead lights.
- ✓ **Compact & clever:** Small, lightweight, and handy – perfect for mobile use
 - ✓ **Full Visibility:** Transparent flap for maximum control – technology becomes visible and tangible
 - ✓ **Intuitive Operation:** 5" color touch display for simple, direct interaction
 - ✓ **Smart Handling:** Automatic slide-out system for effortless MultiCard insertion
 - ✓ **Maximum Flexibility:** Processes full and half MultiCards, as well as individual markers
 - ✓ **Independent Printing:** Execute projects on the go thanks to USB stick and temporary memory
 - ✓ **Durable & Low-Maintenance:** Robust technology for daily use with minimal effort

PrintJet MINI

Your compact industrial printer
for professional marking solutions



The PrintJet MINI is not only compact and lightweight, but also suitable for mobile use.



Supports full and half MultiCards as well as individual marker segments.



The ink cartridge with integrated print head allows for easy cleaning with a simple wipe and can be completely replaced, including the ink, when needed.



Technical data

	Description
Intended use	Printing Weidmüller MultiCards
Technology	Inkjet printing process with integrated UV light curing unit
Feed & Removal	Manual, full card or individual segment
Application site	Office conditions
Ambient temperature	18 °C - 30 °C 64 °F - 86 °F
Dimensions	Length: 540 mm Width: 330 mm Height: 190 mm
Weight	13 kg with packaging 8.5 kg without packaging
Ink system	Cartridge including print head, color: black
Included in delivery	• PrintJet MINI • one MultiCard DEK 5/5 • Desktop power supply, fixed voltage 24 V/DC 3.75 A 90 W • Ink cartridge including cleaning cloth • Mains cable • Downloadable instructions for manual, quick guide, and M-Print® PRO labeling software • USB cable • LAN cable The ink cartridge is not installed in the printer.
Printing speed	about 1,5 minutes per MultiCard
Print resolution, max.	600 DPI
Interface	USB, LAN
Supply voltage	100 - 240 V, 50/60 Hz, 1,3 A

Ordering data

Type	VPE	Order No.
PrintJet MINI	1	3049980000

Accessories

	Type	VPE	Order No.
Ink cartridge black	PJM INK K	1	3062650000
Ink collecting tray	PJM WASTE PAD	1	3062640000
Transport case	PJM TRANSPORT CASE	1	3109810000