



Print  
small label  
volumes  
affordably  
& easily

## Workplace Solutions

# The New PrintJet MINI

Smallest, most affordable UV-ink label printer on the market



As a cabinet manufacturer, system planner or technician, you know how crucial precise and durable labeling is for optimizing processes and ensuring clarity within control cabinet infrastructure.

With the PrintJet MINI — the compact industrial printer from Weidmüller — you're choosing a smart solution that boosts your efficiency and is perfectly tailored to your needs.

The PrintJet MINI is small, lightweight and optionally available with a practical transport case. This mobility option makes the printer the ideal choice for on-site service operations or changing work environments.

### Your benefits at a glance

- **Compact & clever:** Small, lightweight and handy — perfect for mobile use
- **Full visibility:** Transparent flap for maximum control — technology becomes visible
- **Intuitive operation:** 5" color touch display for simple, direct interaction
- **Smart handling:** Automatic slide-out system for effortless MultiCard insertion
- **Maximum flexibility:** Processes full and half MultiCards, as well as individual markers
- **Independent printing:** Execute projects from a USB stick or through the temporary memory
- **Durable & low-maintenance:** Robust technology for daily use with minimal effort



▶ Watch video  
to learn more

# PrintJet MINI

Your compact industrial printer for professional marking solutions



The PrintJet MINI is not only compact and lightweight, but also suitable for mobile use.



Supports full and half MultiCards as well as individual marker segments.



The ink cartridge with integrated print head allows for easy cleaning with a simple wipe and can be completely replaced, including the ink, when needed.

## Technical data

	Description
Intended use	Printing Weidmuller MultiCards
Technology	Inkjet printing process with integrated UV light curing unit
Feed & Removal	Manual, full card or individual segment
Application site	Office conditions
Ambient temperature	18 °C - 30 °C (50 °F - 95 °F)
Dimensions	Length: 540 mm (21.26 in) Width: 330 mm (12.99 in) Height: 190 mm (7.48 in)
Weight	13 kg (28.66 lbs) with packaging 8.5 kg (18.74 lbs) without packaging
Ink system	Cartridge including print head, color: black
Included in delivery	<ul style="list-style-type: none"><li>• PrintJet MINI</li><li>• One MultiCard DEK 5/5</li><li>• Desktop power supply, fixed voltage 24 V/DC 3.75 A 90 W</li><li>• Ink cartridge including cleaning cloth</li><li>• Mains cable</li><li>• Downloadable instructions for manual, quick guide, and M-Print® PRO labeling software</li><li>• USB cable</li><li>• LAN cable</li></ul>
Printing speed	about 1.5 minutes per MultiCard
Print resolution, max.	600 DPI
Interface	USB, LAN
Supply voltage	230 V AC / 16 A, 115 V AC / 20 A

Note: The ink cartridge is not installed in the printer.

## Design Meets Function

With the PrintJet MINI, we've developed more than just an industrial printer — we've created a mobile solution that combines design, functionality and efficiency in a compact format. Thoughtfully designed down to the last detail, it enables precise marking wherever it's needed — flexible, reliable and intuitive.

The PrintJet MINI stands for modern industrial design that not only optimizes processes, but also sets new standards in mobility and user convenience.

## Ordering data

Type	VPE	Order No.
PrintJet MINI	1	3049980000

## Accessories

	Type	VPE	Order No.
Ink cartridge black	PJM INK SW	1	3062650000
Ink collecting tray	PJM WASTE PAD	1	3062640000
Transport case	PJM TRANSPORT CASE	1	3109810000

## Discover the future of Workplace Solutions

Contact us today at [weidmuller.com/sales](http://weidmuller.com/sales) to learn more about how our PrintJet MINI can help you achieve your systemized marking goals.



Discover more