

## HDC DE 0005

### Topic: EUROMAP 67

#### Introduction:


EUROMAP means European Plastics and Rubber Machinery.

With this definition, a consortium of machine manufacturers has identified products that can be used in the various applications.


There are different versions. Version 67 is shown here as an example. Further information on approved components can be sent on request.

#### Europe 67 approved design

##### Plug on handling device



##### Connector for the opposite side



#### Application

Weidmüller offers connectors for this area:

- Connectors for EUROMAP 67: Electrical interface between injection moulding machine and handling device / robot

The design for these connectors can be seen in the illustration on the right.

The connectors approved for this application are listed below.

- Housing not specified with regard to overall height and cable outlet.
- Contact type not specified with regard to material.

Connector housing:			Base or add-on housing:		
<b>Socket insert Z</b> HDC HD 25 FC Z (1023050000)			<b>Socket insert</b> HDC HD 25 (1650820000)		
<b>Pin insert</b> HDC HD 25 MC (1650810000)			<b>Pin insert Z</b> HDC HD 25 MC Z (1023050000)		
<b>Plug housing, cable entry on the side</b> M25: HDC 32A TSBU 1M25G (1787960000) M32: HDC 32A TSBU 1M32G (1787950000)			<b>Add-on housing</b> HDC 32A ABU (1665860000) with cover: HDC 32A ADBO (1666440000)		
<b>Plug housing, cable entry on top</b> M32: HDC 32A TOBU 1M32G (1787990000)			<b>Socket housing</b> M25: HDC 32A SBU 1M25G (1788040000) with cover: HDC 32A SDBO 2M25G (1788060000) Optional further variants with only one insertion, or M32		
<b>Zubehör</b>	<b>Zubehör</b>		<b>Accessories</b>		
<b>Crimpkontakte Stift - Gold</b>	<b>Crimpkontakte Buchse - Gold</b>		<b>Crimp contacts</b>		
HDC-HD-SMD 140.37AU 100 1651620000	HDC-HD-BM0 140.37AU 100 1651670000		HDC-HD-BM0 140.37AG 100 1651570000		
HDC-HD-SMD 5A6 100 1651630000	HDC-HD-BM0.5AU 100 1651680000		HDC-HD-BM0.5AG 100 1651690000		
HDC-HD-SMD 75.100AU 100 1651640000	HDC-HD-BM0.75.100AU 100 1651700000		HDC-HD-BM1.5AU 100 1651710000		
HDC-HD-SM1 5AU 100 1651650000	HDC-HD-BM1.5AG 100 1651720000		HDC-HD-BM2.5AU 100 1651730000		
HDC-HD-SM2 5AU 100 1651660000	HDC-HD-BM2.5AG 100 1651740000				
<b>Crimpkontakte Stift - Silber</b>	<b>Crimpkontakte Buchse - Silber</b>				
HDC-HD-SMD 140.37AG 100 1651520000	HDC-HD-BM0 140.37AG 100 1651580000				
HDC-HD-SMD 5A6 100 1651530000	HDC-HD-BM0.5AG 100 1651590000				
HDC-HD-SMD 75.100AG 100 1651550000	HDC-HD-BM0.75.100AG 100 1651600000				
HDC-HD-SM1 5AG 100 1651560000	HDC-HD-BM1.5AG 100 1651610000				
HDC-HD-SM2 5AG 100 1651570000	HDC-HD-BM2.5AG 100 1651620000				
<b>Werkzeuge</b>	<b>Werkzeuge</b>				
CTX CM 1/6/2.5 1 9018490000	CTX CM 1/6/2.5 1 9018490000				
REMOV. TOOL HD 1 1866730000	REMOV. TOOL HD 1 1866730000				

#### Contact:

Weidmüller Interface GmbH &Co. KG

Klingenbergsstr. 26

32758 Detmold

Tel: 05231 14 29 0

E-mail address for technical questions:

support\_hdc@weidmueller.com