

Klippon® POK – Polyester enclosures

Universal terminal and electronic boxes

Extremely robust, weather and impact resistant

Klippon® POK enclosures are made from high-quality glass fibre reinforced polyester. They are suited for applications and environments where corrosion and impact resistance, as well as high IP protection, are required. The enclosures are available in 17 sizes and two standard finishes - grey for industrial use and black for Ex applications.

Developed to meet the rigorous demands of industrial automation or process control and energy industries and with signal and component protection in mind, the Klippon® POK enclosure range is designed to meet the customers' application needs.



Your special advantages:

- High impact resistance (7 / 10 J) due to high fibreglass content
- Direct fastening of the enclosure via rear side fixing holes outside of the sealing area
- Various mounting options inside the enclosure due to threaded holes inside
- Great temperature resistance from -40°C to +100°C by using silicone sealing
- Usable in industrial and harsh applications as well as in explosive atmospheres
- Worldwide approvals according to the latest international standards including assembled electronic boxes for Ex applications



Product Overview

Description	Height x width x depth in mm	Standard (grey finish)	Ex enclosure (black finish)
Klippon® POK 080806	75 x 80 x 55	1305810000	1306000000
Klippon® POK 081106	75 x 110 x 56	1305820000	1306010000
Klippon® POK 081606	75 x 160 x 56	1305830000	1306020000
Klippon® POK 081906	75 x 190 x 55	1305840000	1306030000
Klippon® POK 082306	75 x 230 x 56	1305850000	1306040000
Klippon® POK 121209	120 x 122 x 90	1305870000	1306050000
Klippon® POK 122209	120 x 220 x 90	1305880000	1306070000
Klippon® POK 161609	160 x 160 x 90	1305890000	1306080000
Klippon® POK 162609	160 x 260 x 90	1305900000	1306090000
Klippon® POK 163609	160 x 360 x 90	1305910000	1306100000
Klippon® POK 165609	160 x 560 x 90	1305920000	1306110000
Klippon® POK 252512	250 x 255 x 120	1305930000	1306120000
Klippon® POK 252516	250 x 255 x 160.5	1305980000	1306170000
Klippon® POK 254012	250 x 400 x 120	1305940000	1306130000
Klippon® POK 254016	250 x 400 x 160.5	1305990000	1306180000
Klippon® POK 256012	250 x 600 x 120	1305950000	1306140000
Klippon® POK 404012	405 x 400 x 120	1305970000	1306150000

Note



For a more detailed overview of the products, you can open the online catalogue at catalogue.weidmueller.com or scan the QR code.



You can find this product family in our Weidmüller Configurator:
www.weidmueller.com/wmc