





HighPower Overview



						45 kN			80 kN		
						 EPG 45 1500830000			 APG 80 2853270000		
Type	Wire gauge	Name	Part number	Gender	Stripping length	Tool insert	Part number	Number of crimps	Tool insert	Part number	Number of crimps
250 A Female  Male 	25mm ²	HDC HP 250 F 25	1079720000	Female	unshielded 	ES EPG 45 HEX 25/50	1500970000	1	ES APG 80 HEX 25	1502640000	1
		HDC HP 250 M 25	1079690000	Male							
	35mm ²	HDC HP 250 F 35	1079730000	Female		ES EPG 45 HEX 16/35	1500950000	1	ES APG 80 HEX 35	1502650000	1
		HDC HP 250 M 35	1079690000	Male							
	50mm ²	HDC HP 250 F 50	1079740000	Female		ES EPG 45 HEX 25/50	1500970000	2	ES APG 80 HEX 50	1502670000	1
		HDC HP 250 M 50	1119080000	Male							
	50mm ²	HDC HP 250 F 50 PE	1220840000	Female	shielded 	ES EPG 45 HEX 25/50	1500970000	2	ES APG 80 HEX 50	1502670000	1
		HDC HP 250 M 50 PE	1220850000	Male							
	70mm ²	HDC HP 250 F 70	1079750000	Female		ES EPG 45 HEX 10/70	1500940000	2	ES APG 80 HEX 70	1502680000	1
		HDC HP 250 M 70	1119090000	Male							
	95mm ²	HDC HP 250 F 95	1079770000	Female		ES EPG 45 HEX 95	1500980000	2	ES APG 80 HEX 95	1502690000	1
		HDC HP 250 M 95	1119100000	Male							
550A Female  Male 	25mm ²	HDC HP 550 F 25	1220570000	Female	unshielded 	ES EPG 45 HEX 25/50	1500970000	1	ES APG 80 HEX 25	1502640000	1
		HDC HP 550 M 25	1220580000	Male							
	50mm ²	HDC HP 550 F 50	1177100000	Female		ES EPG 45 HEX 25/50	1500970000	2	ES APG 80 HEX 50	1502670000	1
		HDC HP 550 M 50	1157800000	Male							
	70mm ²	HDC HP 550 F 70	1268820000	Female		ES EPG 45 HEX 10/70	1500940000	2	ES APG 80 HEX 70	1502680000	1
		HDC HP 550 M 70	1268810000	Male							
	95mm ²	HDC HP 550 F 95	1079810000	Female	shielded 	ES EPG 45 HEX 95	1500980000	2	ES APG 80 HEX 95	1502690000	1
		HDC HP 550 M 95	1079790000	Male							
	120mm ²	HDC HP 550 F 120	1079810000	Female		ES EPG 45 HEX 120	1500990000	2	ES APG 80 HEX 120	1502700000	1
		HDC HP 550 M 120	1079780000	Male							
	150mm ²	HDC HP 550 F 150	1079830000	Female					ES APG 80 HEX 150	1502720000	2
		HDC HP 550 M 150	1119110000	Male							
	185mm ²	HDC HP 550 F 185	1079840000	Female					ES APG 80 HEX 185	1502730000	2
		HDC HP 550 M 185	1120580000	Male							
	240mm ²	HDC HP 550 F 240	1120600000	Female					ES APG 80 HEX 240	1502740000	2
		HDC HP 550 M 240	1120590000	Male							