







KLBÜ SC

Weidmüller Interface GmbH & Co. KG
Postfach 3030
32720 Detmold
Klingenbergstraße 16
32758 Detmold
Telefon +49 (0) 5231 14-0
Telefax +49 (0) 5231 14-292083
E-Mail: info@weidmueller.com
Internet: www.weidmueller.com

Drilling template KLBÜ 15-32 SC



KLBÜ SC










KLBÜ SC

KLBÜ CO







KLBÜ

Weidmüller










Type	Ø	(a x b x c x d x e) mm	Order No.
KLBÜ 3-8 SC	3.0 ... 8.0 mm	13.5 x 11.5 x 18.0 x 26.0 x 5.65	1692261001
KLBÜ 4-13.5 SC	4.0 ... 13.5 mm	20.0 x 17.8 x 20.3 x 31.4 x 5.30	1712311001
KLBÜ 10-20 SC	10.0 ... 20.0 mm	24.8 x 23.0 x 26.0 x 40.0 x 5.30	1712321001
KLBÜ 15-32 SC	15.0 ... 2.0 mm	36.0 x 33.3 x 32.0 x 64.0 x 4.80	1718341001
Operating tool		Qty.	Order No.
BTWZ KLBÜ		1	1742630000





Type	Ø	(a x b x c x d) mm	Order No.
KLBÜ CO 1	3.0 ... 10.0 mm	18.0 x 12.0 x 13.2 x 32.0	1753311001
KLBÜ CO 2	4.0 ... 15.0 mm	18.0 x 20.0 x 21.1 x 41.6	1752131001
KLBÜ CO 3	10.0 ... 20.0 mm	25.0 x 23.0 x 24.0 x 45.0	1749151001
KLBÜ CO 4	15.0 ... 28.0 mm	25.0 x 31.0 x 32.0 x 56.0	1749161001
KLBÜ CO 5	20.0 ... 37.0 mm	32.0 x 40.0 x 42.7 x 64.5	1755081001



Type	Ø	(a x b x c) mm	Order No.
KLBÜ 2 x 2-6	2.0 ... 6.0 mm	15.0 x 18.0 x 24.0	1675350000
KLBÜ 3-8	3.0 ... 8.0 mm	13.0 x 18.0 x 26.0	1600480000
KLBÜ 4-13.5	4.0 ... 13.5 mm	20.0 x 20.5 x 31.5	1592810000
KLBÜ 10-20	10.0 ... 20.0 mm	25.0 x 26.0 x 40.0	1600490000
KLBÜ 15-32	15.0 ... 32.0 mm	36.0 x 32.0 x 63.9	1716300000